

Tehničke karakteristike proizvoda

Karakteristike

13442

mini Mureva - za modularni uređaj - 1 otvor - 6
modula - 2 priključna bloka



Osnovne informacije

Grupa proizvoda	Mureva
Ime proizvoda	Mureva Enclosure
Tip proizvoda ili komponente	Orman
Tip ormara	Mini ormar za modularne uređaje
Opis montažne ploče	Bez montažne ploče

Dopunske informacije

Montaža ormara	Površinska
9 mm redovi	12
Broj 18 mm modula po redu	6
Ukupan broj 18 mm modula	6
Broj horizontalnih redova	1
Električna klasa izolacije	Dupla izolacija Klasa II
Obezbeđena oprema	1 set oznaka 2 sabirnica 4 izvoda
Tip prednjeg poklopca	Providni
Snaga disipacije u w	11 W
[in] nazivna struja	63 A
Tip šine	DIN
Broj otvora pg iso	3
Broj priključnih blokova	2 uzemljenje/nula (priključak na zavrtanj) sa 4 izvodi
Izvodi razvodnog bloka	4 x 10 mm ² 4 x 16 mm ²
Opis opcija zaključavanja	Opciona bravica
Materijal kućišta	Samogasivi polimer
Širina	159 mm
Visina	200 mm
Dubina	112 mm
Unutrašnja dubina	56 mm
Boja	Vrata: prozirnazelena Orman: svetlosiva (RAL 7035)

Okruženje

Standardi	EN 50262 IEC 61439-3 IEC 60695-2-1 IEC 60670
Otpornost na vatru	650 °C u skladu sa IEC 60695-2-1
Ip stepen zaštite	IP65 u skladu sa IEC 60529
Ik stepen zaštite	IK09 u skladu sa EN 50102
Environmental characteristics (UV)	UV otpornost: klasa 3 u skladu sa ISO 4582:2010 Test ultraljubičaste degradacije u skladu sa ISO 4892-2:2013
Kategorija prenapona	II
Temperatura okoline za rad uređaja	-25...60 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11,000 cm
Package 1 Width	16,000 cm
Package 1 Length	20,000 cm
Package 1 Weight	599,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	7
Package 2 Height	22,000 cm
Package 2 Width	34,000 cm
Package 2 Length	40,500 cm
Package 2 Weight	4,569 kg
Unit Type of Package 3	P12
Number of Units in Package 3	168
Package 3 Height	80,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	120,360 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Učinak u vezi sa sadržajem halogena	Proizvod bez halogena
Minimum percentage of recycled plastic content	25

Ugovorna garancija

Garancija	18 meseci
-----------	-----------