

Tehničke karakteristike proizvoda

Karakteristike

19066

naponski okidač - MX - od - 24 V AC



Osnovne informacije

Grupa proizvoda	Acti 9
Tip proizvoda ili komponente	Naponski okidač sa OC kontaktom
Kratko ime uređaja	MX + OF
Signalni kontakt	1 C/O
[in] nazivna struja	0,1...6 A at <= 240 V, AC 0,1...3 A at <= 48 V, DC
Napon upravljačkog kola	24 V AC 50/60 Hz 24 V DC
9 mm redovi	2

Dopunske informacije

Kompatibilnost grupe proizvoda	Acti 9 Vigi NG125 Acti 9 Acti 9 NG125LMA Acti 9 Acti 9 NG125NA Acti 9 Acti 9 NG125
[ui] nazivni napon izolacije	690 V AC 50/60 Hz u skladu sa EN/IEC 60947-5-1
[uimp] nazivni podnosivi impulsni napon	8 kV u skladu sa EN/IEC 60947-5-1
Lokalna signalizacija	Indikator akcije
Način montiranja	Fiksno
Nosači za montažu	35 mm simetrična DIN šina
Visina	105 mm
Širina	32 mm
Dubina	78 mm
Masa proizvoda	0,132 kg
Električna trajnost	10000 ciklusa u skladu sa EN/IEC 60947-5-1
Povezivanje - priključci	Pločasti priključak - 1 kabl(ovi) 0,5...2,5 mm ² - kruti Pločasti priključak - 1 kabl(ovi) 0,5...1,5 mm ² - fleksibilni Pločasti priključak - 1 kabl(ovi) 0,5...1,5 mm ² - fleksibilni sa kablovskim završetkom Pločasti priključak - 2 kabl(ovi) 2,5 mm ² - fleksibilni Pločasti priključak - 2 kabl(ovi) 2,5 mm ² - kruti Pločasti priključak - 2 kabl(ovi) 1,5 mm ² - fleksibilni sa kablovskim završetkom
Dužina ogoljenog dela žice	10 mm
Moment pritezanja	1 N.m
Kompatibilnost	MX + OF

Okruženje

Standardi	EN/IEC 60947-5-1
Sertifikacija proizvoda	EAC
Ip stepen zaštite	IP20 B u skladu sa EN/IEC 60947-5-1 IP4 u skladu sa EN/IEC 60947-5-1
Stepen zaprljanosti	3 u skladu sa EN/IEC 60947-5-1
Kategorija prenapona	II
Tropikalizacija	2 u skladu sa EN/IEC 60947-5-1
Relativna vlažnost	95 % pri 55 °C

Temperatura okoline za rad uređaja	-25...60 °C
Temperatura okoline za skladištenje	-40...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,200 cm
Package 1 Width	7,800 cm
Package 1 Length	10,500 cm
Package 1 Weight	124,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	11,200 cm
Package 2 Width	8,500 cm
Package 2 Length	23,500 cm
Package 2 Weight	807,000 g
Unit Type of Package 3	S03
Number of Units in Package 3	54
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	7,740 kg

Održivost ponude

Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 months
-----------	-----------