

Tehničke karakteristike proizvoda Karakteristike

28904 rastavljač Compact INS80 - 3P - 80 A



Osnovne informacije

Grupa proizvoda	Compact
Ime proizvoda	Compact INS
Tip proizvoda ili komponente	Rastavljač
Broj polova	3P
Tip mreže	DC AC
Mrežna frekvencija	50/60 Hz
[ie] nazivna struja	AC-23A: 40 A AC 50/60 Hz 500 V AC-23A: 63 A AC 50/60 Hz 440/480 V 2 pola serijski AC-22A: 80 A AC 50/60 Hz 220/240 V AC-22A: 80 A AC 50/60 Hz 380/415 V AC-22A: 80 A AC 50/60 Hz 440/480 V AC-22A: 80 A AC 50/60 Hz 500 V AC-23A: 72 A AC 50/60 Hz 380/415 V AC-23A: 80 A AC 50/60 Hz 220/240 V DC-22A: 80 A DC 50/60 Hz 125 V 2 pola serijski DC-23A: 80 A DC 125 V 2 pola serijski
[ui] nazivni napon izolacije	690 V AC 50/60 Hz
[uimp] nazivni podnosivi impulsni napon	8 kV
[ith] dozvoljena termička struja u vazduhu	80 A pri 60 °C
[icm] nazivna kratkospojna moć uključenja	15 KA sam rastavljač 500 V AC pri 50/60 Hz 75 kA sa zaštitnim prekidačem 500 V AC pri 50/60 Hz
[ue] nazivni napon	125 V DC 500 V AC 50/60 Hz
Pogodno za izolaciju	Da
Indikator pozicije kontakta	Da
Vidljivo prekidanje	Ne
Stepen zaprljanosti	3

Dopunske informacije

Tip upravljanja	Zakretna ručica
Boja drške	Crna
Način montiranja	Fiksno
Nosači za montažu	Ploča DIN šina
Gornji priključak	Prednja
Donji priključak	Prednji
Poprečni presek kablova	1,5...50 mm ²
Maksimalna snaga	AC-23: 22 kW pri 500/525 V AC 50/60 Hz AC-23: 22 kW pri 220/240 V AC 50/60 Hz AC-23: 37 kW pri 380/415 V AC 50/60 Hz AC-23: 37 kW pri 440 V AC 50/60 Hz
Nazivni ciklus	Neprekidno
Klasa rada sa prekidima	Klasa 120 - 60 %
Dimenzije kućišta za ithe	190 mm x 115 mm x 55 mm

[icw] kratkotrajna podnosiva struja kratkog spoja	0,067 KA tokom 20 s u skladu sa IEC 60947-3 1,73 KA tokom 3 s u skladu sa IEC 60947-3 3 KA tokom 1 s u skladu sa IEC 60947-3 5,5 kA tokom 30 s u skladu sa IEC 60947-3
Mehanička trajnost	20000 ciklusa
Električna trajnost	AC-22A: 1500 ciklusa 220/240 V AC 50/60 Hz AC-22A: 1500 ciklusa 380/415 V AC 50/60 Hz 2 pola serijski AC-22A: 1500 ciklusa 440 V AC 50/60 Hz AC-22A: 1500 ciklusa 500 V AC 50/60 Hz AC-23A: 1500 ciklusa 220/240 V AC 50/60 Hz AC-23A: 1500 ciklusa 380/415 V AC 50/60 Hz AC-23A: 1500 ciklusa 440 V AC 50/60 Hz AC-23A: 1500 ciklusa 500 V AC 50/60 Hz DC-22A: 1500 ciklusa 250 V DC 50/60 Hz 2 pola serijski DC-23A: 1500 ciklusa 250 V DC 2 pola serijski
Povezivanje	18 mm
Visina	85 mm
Širina	90 mm
Dubina	62,5 mm
Masa proizvoda	0,5 kg

Okruženje

Standardi	IEC 60947-3 IEC 60947-1
Sertifikacija proizvoda	CCC[RETURN]KEMA-KEUR
Ip stepen zaštite	IP40 conforming to IEC 60529
Ik stepen zaštite	IK07 conforming to EN 50102
Temperatura okoline za rad uređaja	-25...70 °C
Temperatura okoline za skladištenje	-50...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9,300 cm
Package 1 Width	10,000 cm
Package 1 Length	10,000 cm
Package 1 Weight	600,000 g
Unit Type of Package 2	S03
Number of Units in Package 2	18
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	11,200 kg
Unit Type of Package 3	P12
Number of Units in Package 3	144
Package 3 Height	50,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	103,160 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu

Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------