

Tehničke karakteristike proizvoda

Karakteristike

48214

motorni pogon - MCH - 380..415 V AC



Osnovne informacije

| | |
|--------------------------------|-------------------------------------|
| Kratko ime uređaja | Motorni pogon MCH |
| Tip proizvoda ili komponente | Motorni pogon MCH |
| Primena uređaja | Navijanje automatske opruge |
| Kompatibilnost grupe proizvoda | Masterpact (Masterpact NW) prekidač |
| Tip upravljanja | Motorni mehanizam |
| Napon upravljačkog kola | 380...415 V AC 50/60 Hz |
| Circuit breaker mounting mode | Fiksno |





Dopunske informacije

| | |
|---------------------------|-----------|
| Maksimalno vreme punjenja | 4 sekundi |
| Maksimalna potrošnja u va | 180 VA |

Pakovanje

| | |
|------------------------------|------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 12,500 cm |
| Package 1 Width | 13,000 cm |
| Package 1 Length | 23,000 cm |
| Package 1 Weight | 1,918 kg |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 3 |
| Package 2 Height | 15,000 cm |
| Package 2 Width | 30,000 cm |
| Package 2 Length | 40,000 cm |
| Package 2 Weight | 6,014 kg |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 48 |
| Package 3 Height | 45,000 cm |
| Package 3 Width | 80,000 cm |
| Package 3 Length | 120,000 cm |
| Package 3 Weight | 108,224 kg |

Održivost ponude

| | |
|------------------------------|--------------------------------------------------------------------------------------------------------------------|
| Propis REACH |  REACH Deklaracija |
| EU RoHS direktiva | Usaglašeno  EU RoHS Deklaracija |
| Bez žive | Da |
| RoHS regulativa za Kinu |  RoHS Deklaracija Za Kinu |
| Informacije o RoHS izuzecima |  Da |

Ugovorna garancija

Garancija

18 meseci
