

Tehničke karakteristike proizvoda Karakteristike

48259

prekidač Masterpact NW12H1 - 1250 A - 3P - izvlačivi - bez zaštitne jedinice



Osnovne informacije

Grupa proizvoda	Masterpact NW
Tip proizvoda ili komponente	Osnovni ram
Kratko ime uređaja	Masterpact NW12
Ime prekidača	Masterpact NW12H1
Broj polova	3P
Tip mreže	AC
Kod prekidne moći	H1
Pogodno za izolaciju	Yes conforming to IEC 60947-2
Kategorija upotrebe	Kategorija B

Dopunske informacije

Mrežna frekvencija	50/60 Hz
Tip upravljanja	Taster
Način montiranja	Izvlačivo
[in] nazivna struja	1250 A at 40 °C
[ui] nazivni napon izolacije	1000 V AC 50/60 Hz conforming to IEC 60947-2
[uimp] nazivni podnosivi impulsni napon	12 kV conforming to IEC 60947-2
[icm] nazivna kratkospojna moć uključivanja	143 KA 525 V AC at 50/60 Hz 143 kA 690 V AC at 50/60 Hz
[ue] nazivni napon	690 V AC 50/60 Hz conforming to IEC 60947-2
Ct veličina prekidača	1250 A
Prekidna moć	65 KA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 65 KA Icu at 690 V AC 50/60 Hz conforming to IEC 60947-2 65 KA Icu pri 440 V AC 50/60 Hz u skladu sa IEC 60947-2 65 KA Icu at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 380...415 V AC 50/60 Hz conforming to IEC 60947-2
[ics] servisna prekidna moć	65 KA at 525 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 690 V AC 50/60 Hz conforming to IEC 60947-2
Tip zaštite	Bez zaštite
Mehanička trajnost	12500 Cycles without maintenance conforming to IEC 60947-2 25000 cycles with maintenance conforming to IEC 60947-2
Električna trajnost	10000 Cycles 440 V AC 50/60 Hz without maintenance conforming to IEC 60947-2 10000 Cycles 690 V AC 50/60 Hz without maintenance conforming to IEC 60947-2 AC-23A: 10000 cycles 440 V AC 50/60 Hz without maintenance conforming to IEC 60947-2 AC-23A: 10000 cycles 690 V AC 50/60 Hz without maintenance conforming to IEC 60947-2 AC-3: 6000 cycles 440/690 V AC 50/60 Hz without maintenance conforming to IEC 60947-2
Povezivanje	115 mm
[icw] kratkotrajna podnosiva struja kratkog spoja	36 KA 3 s u skladu sa IEC 60947-2 65 kA 1 s u skladu sa IEC 60947-2
Maksimalno vreme prekidanja	25 milisekundi
Maksimalno odzivno vreme zatvaranja	70 milisekundi
Visina	439 mm

Širina	441 mm
Dubina	394,5 mm

Okruženje

Standardi	IEC 60947-2
Sertifikacija proizvoda	ASTA
Stepen zaprijanosti	4 conforming to IEC 60664-1
Temperatura okoline za rad uređaja	-25...70 °C
Temperatura okoline za skladištenje	-40...85 °C

Packing Units

Tip jedinice pakovanja 1	PCE
Broj jedinica u pakovanju 1	1
Pakovanje 1 težina	47,036 kg
Pakovanje 1 visina	30,5 cm
Pakovanje 1 širina	29,5 cm
Pakovanje 1 dužina	37,5 cm

Offer Sustainability

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez žive	Da
Informacije o RoHS izuzecima	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Bez PVC	Da

Contractual warranty

Garancija	18 months
-----------	-----------