

Tehničke karakteristike proizvoda

Karakteristike

GV2AP01

TeSys GV2 - set okretne ručice - IP54 - crni -
za GV2L & GV2P



Osnovne informacije

Grupa proizvoda	TeSys
Kratko ime uređaja	GV2AP
Tip proizvoda ili komponente	Set zakretne ručice
Pribor / posebna kategorija	Pribor za upravljanje
Boja drške	Crna
Boja prednje pločice sa ručicom	Plava

Dopunske informacije

Kompatibilnost proizvoda	GV2L GV2P
Zaključavanje zakretne ručice	Zaključavanje u OFF poziciji Zaključavanje u ON poziciji
Način montaže zakretne ručice	Produžena
Opis opcija zaključavanja	1 do 3 katanca
Udaljenost od zadnjeg dela/vrata	150...290 mm
Masa proizvoda	0,2 kg

Okruženje

Ip stepen zaštite	IP54
-------------------	------

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13,0 cm
Package 1 Width	12,5 cm
Package 1 Length	20,0 cm
Package 1 Weight	223,0 g
Unit Type of Package 2	S04
Number of Units in Package 2	16
Package 2 Height	30,0 cm
Package 2 Width	40,0 cm
Package 2 Length	60,0 cm
Package 2 Weight	4,82 kg
Unit Type of Package 3	P06
Number of Units in Package 3	64
Package 3 Height	77,0 cm
Package 3 Width	80,0 cm
Package 3 Length	60,0 cm
Package 3 Weight	27,78 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------