

Tehničke karakteristike proizvoda

Karakteristike

GV2APN02

TeSys GV2 - set okretne ručice - IP54 - crvena
- za GV2L & GV2P



Osnovne informacije

Grupa proizvoda	TeSys TeSys Deca
Kratko ime uređaja	GV2AP
Tip proizvoda ili komponente	Set zakretne ručice
Pribor / posebna kategorija	Pribor za upravljanje
Boja drške	Crvena
Boja prednje pločice sa ručicom	Žuta

Dopunske informacije

Kompatibilnost proizvoda	GV2L GV2P
Zaključavanje zakretne ručice	Zaključavanje u OFF poziciji
Način montaže zakretne ručice	Produžena
Opis opcija zaključavanja	1 do 3 katanca
Udaljenost od zadnjeg dela/vrata	140...250 mm
Masa proizvoda	0,3 kg

Okruženje

Ip stepen zaštite	IP54
-------------------	------

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,600 cm
Package 1 Width	8,900 cm
Package 1 Length	37,100 cm
Package 1 Weight	349,000 g
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	4,736 kg
Unit Type of Package 3	P06
Number of Units in Package 3	96
Package 3 Height	77,000 cm
Package 3 Width	80,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	46,260 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 months
-----------	-----------