

Tehničke karakteristike proizvoda

Karakteristike

ISM20817

OptiLine 45 OptiLine 70 - podna kanalica - siva



Osnovne informacije

Kablovski instalacioni sistem	Stub Stubić
Tip proizvoda ili komponente	Podna kanalica

Dopunske informacije

Tip stuba	Jednostrano Dve instalacione kutije Dvostrano Jedna instalaciona kutija
Tip stuba	Jednostrani Dvostrani
Nijansa boje	Siva (RAL 7030)
Količina po setu	28 m
Završna obrada stuba/stubića	Anodička oksidacija Presvučen prahom
Način montaže stuba	Napregnut
Način pričvršćivanja	Sa zavrtnjima bez matice
Materijal	PVC (polivinil-hlorid)
Dužina	2000 mm
Visina	18 mm
Širina	75 mm
Segment tržišta	Male komercijalne zgrade Stambene zgrade

Okruženje

Standardi	EN 50085-1:2005 NF C 68-102
Temperatura okoline za rad uređaja	-25...60 °C
Ip stepen zaštite	IP30

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	2
Package 1 Height	2,0 cm
Package 1 Width	8,5 cm
Package 1 Length	200,0 cm
Package 1 Weight	1,06 kg
Unit Type of Package 2	BB1

Number of Units in Package 2	28
Package 2 Height	9,0 cm
Package 2 Width	21,0 cm
Package 2 Length	202,0 cm
Package 2 Weight	15,0 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	448
Package 3 Height	65,0 cm
Package 3 Width	120,0 cm
Package 3 Length	210,0 cm
Package 3 Weight	261,0 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------