

Tehničke karakteristike proizvoda

Karakteristike

ISM50524

OptiLine 45 - Unica podna kutija - 4 modula



Osnovne informacije

Kablovski instalacioni sistem	Podne kutije
Product type	Unica podna kutija
Tip poda	Betonski pod Pod sa šupljinama Dupli pod
Oblik podne kutije	Kvadratna
Colour	Siva (RAL 7011)
Quantity package 1 / unit	1 deo

Dopunske informacije

Broj modula	4 modula
Product material	Čelik PA6 PBT (polibutilen-tereftalat)
Dužina	199 mm
Visina	72 mm
Širina	199 mm

Okruženje

Standardi	73/23/EEC 93/68/EEC IEC 61084-1:ed. 1, 1991 IEC 61084-2-2:2003
Operating temperature	-25...60 °C
Ip stepen zaštite	IP20

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,0 cm
Package 1 Width	21,4 cm
Package 1 Length	21,6 cm
Package 1 Weight	1,084 kg
Unit Type of Package 2	P12
Number of Units in Package 2	150
Package 2 Height	100,0 cm
Package 2 Width	120,0 cm
Package 2 Length	80,0 cm
Package 2 Weight	172,8 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------