

Tehničke karakteristike proizvoda

Karakteristike

ISM50800

OptiLine 45 - dozna - 2 uska/1 široki element



Osnovne informacije

Grupa proizvoda	OptiLine
Kabloski instalacioni sistem	Podne kutije
Product type	Dozna
Tip poda	Dupli pod Pod sa šupljinama Betonski pod
Oblik podne kutije	Pravougaona Kvadratna
Colour	Plava (RAL 5003)
Quantity package 1 / unit	10 delova

Dopunske informacije

Suitable for	Za 1-2 utičnice
Broj modula	2 modula
Product material	PA6
Dužina	126 mm
Visina	23 mm
Širina	64 mm

Okruženje

Operating temperature	-25...60 °C
Ip stepen zaštite	IP20

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,3 cm
Package 1 Width	6,4 cm
Package 1 Length	12,6 cm
Package 1 Weight	24,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5,0 cm
Package 2 Width	24,0 cm
Package 2 Length	31,0 cm
Package 2 Weight	243,0 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	3,406 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	REACh Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Pehvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 months
-----------	-----------