

Tehničke karakteristike proizvoda

Karakteristike

LAD4RC3N

D40A do D65A RC 380-415V prigušivač



Osnovne informacije

Grupa proizvoda	TeSys TeSys Deca
Kratko ime uređaja	LAD4
Tip proizvoda ili komponente	Prigušivač
Kompatibilnost proizvoda	3P LC1D40A...D80A 4P LC1DT60A...DT80A

Dopunske informacije

Lokacija za montiranje	Prednji deo
Način montiranja	Stezaljkom
Tehnologija prigušenja	RC kolo
Napon upravljačkog kola	380...415 V AC
Maksimalni vršni napon	3 Uc
Masa proizvoda	0,02 kg
Boja	Tamnosiva

Okruženje

Standardi	IEC 60947-5-1 EN 60947-5-1 CSA C22.2 No 60947-5-1 UL 60947-5-1 GB/T 14048.5
Sertifikacija proizvoda	UL[RETURN]CSA
Ip stepen zaštite	IP2x u skladu sa IEC 60529
Temperatura okoline za rad uređaja	-25...55 °C
Temperatura okoline za skladištenje	-40...80 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,000 cm
Package 1 Width	3,000 cm
Package 1 Length	6,000 cm
Package 1 Weight	21,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6,300 cm
Package 2 Width	7,300 cm
Package 2 Length	12,000 cm
Package 2 Weight	230,000 g

Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	15,000 cm
Package 3 Width	15,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	2,458 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------