

Tehničke karakteristike proizvoda

Karakteristike

LVSSDP724

PrismaSet S puna vrata 7red.



Osnovne informacije

Grupa proizvoda	PrismaSeT
Tip proizvoda ili komponente	Vrata
Pribor / posebna kategorija	Pribor ormana
Kompatibilnost grupe proizvoda	PrismaSeT S

Dopunske informacije

Montaža ormana	Površinska
Broj ključa	Broj da bude naveden
Tip vrata	Ravna
Namena proizvoda	Orman
Broj horizontalnih redova	7
9 mm redovi	48
Broj 18 mm modula po redu	24
Ukupan broj 18 mm modula	168,0
Masa proizvoda	8,900 kg
Materijal kućišta	Metal
Širina	568 mm
Visina	1246 mm
Dubina	48,4 mm
Boja	Bela (RAL 9003)
Segment tržišta	Stambene zgrade Male zgrade

Okruženje

Ip stepen zaštite	IP41
Ik stepen zaštite	IK08
Temperatura okoline za rad uređaja	-25...60 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,0 cm
Package 1 Width	59,0 cm
Package 1 Length	156,0 cm
Package 1 Weight	11,26 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	22
Package 2 Height	101,0 cm

Package 2 Width	120,0 cm
Package 2 Length	160,0 cm
Package 2 Weight	269,0 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Učinak u vezi sa sadržajem halogena	Proizvod bez halogena