

Tehničke karakteristike proizvoda

Karakteristike

MGU3.023.18

Unica - 1 utičnica - 2P+E, zaštita, italijanski
standard - 1 m - bela



Osnovne informacije

Grupa proizvoda	Unica
Tip proizvoda ili komponente	Utičnica
Ime dekorativnog elementa	Unica (standardna estetika)
Prezentacija uređaja	Mehanizam
Montaža uređaja	Ugradno
Broj utičnica	1
Konfiguracija polova utičnice	2P + E
Outlet standard deviation	Italian
Opis standarda utičnice	Uzemljenje na sredini
Nazivna struja	16 A

Dopunske informacije

Primena uređaja	Napajanje
Tip poklopca	Sa poklopcem
[ue] nazivni napon	250 V
Tip mreže	AC
Mrežna frekvencija	50/60 Hz
Broj modula	1 modul
Način pričvršćivanja	Utično
Nijansa boje	Bela (RAL 9003)
Povezivanje - priključci	Vijčani priključci
Poprečni presek kabla	0...4 Mm ² - krutost kabla: fleksibilni 0...4 mm ² - krutost kabla: kruti
Minimalna moć isključenja opterećenja	100 operacija 1.25 In i 1.1 Un, cos phi = 0,6
Električna trajnost	10000 ciklusa, cos phi = 0,8
Otpornost izolacije	> 5 MOhm pri 500 V
Dielektrična snaga	2000 V
Materijal	ASA + PC: mehanizam poklopca
Završna obrada	Blistav
Količina po setu	Set od 1 blister
Sertifikacija proizvoda	FR.ME63.B02375 AC
Dubina za ugradnju	24 mm
Dubina	33 mm
Širina	22,5 mm
Visina	45 mm
Masa proizvoda	0,0228 kg
Obrada površine	Neobrađeno

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamenjena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovde navedenih informacija.

Okruženje

Temperatura okoline za rad uređaja	15...30 °C
Temperatura okoline za skladištenje	0...35 °C
Ik stepen zaštite	IK01
Ip stepen zaštite	IP20
Karakteristike životne sredine	Izbeljivač Tečni sapun Aceton Tečnost za čišćenje prozora Alkohol Benzin Ulje UV otpornost

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,000 cm
Package 1 Width	6,500 cm
Package 1 Length	6,500 cm
Package 1 Weight	28,500 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4,500 cm
Package 2 Width	13,500 cm
Package 2 Length	33,500 cm
Package 2 Weight	351,000 g
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Height	15,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	1,634 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------