

## Tehničke karakteristike proizvoda

### Karakteristike

## MGU3.226.18

Unica - potezni taster sa kanapom - 10A 250V  
AC - 2 m - beli



### Osnovne informacije

Grupa proizvoda	Unica
Tip proizvoda ili komponente	Potezni prekidač
Ime dekorativnog elementa	Unica (standardna estetika)
Prezentacija uređaja	Mehanizam
Primena uređaja	Upravljanje
Funkcija prekidača	Jednopolni izborni
Nazivna struja	10 A
Izvršni organ	Potezni taster
Broj modula	2 modula
Način pričvršćivanja	Utično
Nijansa boje	Bela (RAL 9003)

### Dopunske informacije

Vrsta tehnologije	Elektromehanička
Dužina kabla	1 m
[ue] nazivni napon	250 V
Tip mreže	AC
Mrežna frekvencija	50/60 Hz
Udaljenost otvaranja	> 3 mm
Povezivanje - priključci	Priključci bez zavrtnjeva
Poprečni presek kabla	2,5 Mm <sup>2</sup> fleksibilni kabl 2,5 mm <sup>2</sup> kruti kabl
Minimalna moć isključenja opterećenja	200 operacija 1.25 In i 1.1 Un, cos phi = 0,3
Električna trajnost	40000 ciklusa, cos phi = 0,6
Dielektrična snaga	2000 V
Otpornost izolacije	> 5 MOhm pri 500 V
Materijal	ASA + PC: mehanizam poklopca
Standardi	LV direktiva EN 60669-1 EMC direktiva
Temperatura okoline za rad uređaja	25...35 °C
Temperatura okoline za skladištenje	0...50 °C
Dubina za ugradnju	22 mm
Dubina	34 mm
Širina	45 mm
Visina	45 mm
Masa proizvoda	0,0291 kg

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovenavedenih informacija.

## Okruženje

Ik stepen zaštite	IK01
Ip stepen zaštite	IP20
Karakteristike životne sredine	Ulje Alkohol Tečnost za čišćenje prozora UV otpornost Aceton Izbeljivač Tečni sapun Benzin

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,0 cm
Package 1 Width	5,0 cm
Package 1 Length	7,0 cm
Package 1 Weight	30,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12,7 cm
Package 2 Width	12,4 cm
Package 2 Length	18,5 cm
Package 2 Weight	374,0 g
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Height	15,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	1,814 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	<a href="#">REACh Deklaracija</a>
REACh bez SVHC	Da
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

## Ugovorna garancija

Garancija	18 months
-----------	-----------