

Tehničke karakteristike proizvoda

Karakteristike

MGU3.862.12

Unica Top/Class - kablovski otvor - 16 A - 2 m - grafit



Osnovne informacije

Grupa proizvoda	Unica
Pribor / posebna kategorija	Pribor za kabliranje
Tip proizvoda ili komponente	Priključak kabla
Ime dekorativnog elementa	Unica Top - Unica Class
Prezentacija uređaja	Mehanizam
Broj modula	2 modula
Način pričvršćivanja	Utično
Zaštitna oprema	Stezaljke protiv izvlačenja
Nijansa boje	Grafit

Dopunske informacije

Kompatibilnost grupe proizvoda	Unica
Nazivna struja	16 A
Povezivanje - priključci	Vijčani priključci
Kapacitet priključaka	≤ 3 x 2.5 mm ² za fleksibilni kabl(ovi) ≤ 3 x 2.5 mm ² za kruti kabl(ovi)
Materijal	ASA + PC: mehanizam poklopca
Sertifikacija proizvoda	ES.ME01.B02319 AC[RETURN]CE[RETURN]EAC
Temperatura okoline za rad uređaja	15...30 °C
Temperatura okoline za skladištenje	0...35 °C
Širina	45 mm
Visina	45 mm
Masa proizvoda	0,0178 kg

Okruženje

Ik stepen zaštite	IK01
Ip stepen zaštite	IP40
Karakteristike životne sredine	Aceton Alkohol Tečnost za čišćenje prozora UV otpornost Benzin Ulje Tečni sapun Izbeljivač

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,9 cm
Package 1 Width	6,4 cm
Package 1 Length	6,7 cm
Package 1 Weight	20,0 g

Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5,0 cm
Package 2 Width	13,0 cm
Package 2 Length	34,0 cm
Package 2 Weight	264,0 g
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Height	15,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	1,364 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------