

Tehničke karakteristike proizvoda

Karakteristike

MGU3.862.25

Unica - kablovski otvor - 16 A - 2 m - krem



Osnovne informacije

Grupa proizvoda	Unica
Pribor / posebna kategorija	Pribor za kabliranje
Tip proizvoda ili komponente	Priključak kabla
Ime dekorativnog elementa	Unica (standardna estetika)
Prezentacija uređaja	Mehanizam
Broj modula	2 modula
Način pričvršćivanja	Utično
Zaštitna oprema	Stezaljke protiv izvlačenja
Nijansa boje	Krem (RAL 9010)

Dopunske informacije

Kompatibilnost grupe proizvoda	Unica
Nazivna struja	16 A
Povezivanje - priključci	Vijčani priključci
Kapacitet priključaka	≤ 3 x 2.5 mm ² za fleksibilni kabl(ovi) ≤ 3 x 2.5 mm ² za kruti kabl(ovi)
Materijal	ASA + PC: mehanizam poklopca
Sertifikacija proizvoda	ES.ME01.B02319 AC[RETURN]CE[RETURN]EAC
Temperatura okoline za rad uređaja	15...30 °C
Temperatura okoline za skladištenje	0...35 °C
Širina	45 mm
Visina	45 mm
Masa proizvoda	0,0178 kg

Okruženje

Ik stepen zaštite	IK01
Ip stepen zaštite	IP40
Karakteristike životne sredine	Tečnost za čišćenje prozora Izbeljivač Aceton Benzin Ulje Alkohol Tečni sapun UV otpornost

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,000 cm
Package 1 Width	6,500 cm
Package 1 Length	6,500 cm
Package 1 Weight	19,800 g
Unit Type of Package 2	BB1

Number of Units in Package 2	10
Package 2 Height	4,500 cm
Package 2 Width	13,500 cm
Package 2 Length	33,500 cm
Package 2 Weight	264,000 g
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Height	15,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	1,288 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------