

## Tehničke karakteristike proizvoda

### Karakteristike

## MUR39911

Mureva Styl - nadgradna kutija - jednostruka - bela



### Osnovne informacije

|                                |                   |
|--------------------------------|-------------------|
| Grupa proizvoda                | Mureva Styl       |
| Tip proizvoda ili komponente   | Montažna kutija   |
| Kompatibilnost grupe proizvoda | Mureva Styl orman |
| Nijansa boje                   | Bela (RAL 9003)   |

### Dopunske informacije

|                                            |                                                                                                                                                                                                                                                                                                                                    |
|--------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Montaža uređaja                            | Nadgradno                                                                                                                                                                                                                                                                                                                          |
| Broj grupa                                 | Jednostruki                                                                                                                                                                                                                                                                                                                        |
| Kablovski uvod                             | Jednostavan pristup ventila                                                                                                                                                                                                                                                                                                        |
| Uslovi upotrebe                            | U zatvorenom/na otvorenom                                                                                                                                                                                                                                                                                                          |
| Materijal                                  | SEBS<br>PP (polipropilen)                                                                                                                                                                                                                                                                                                          |
| Dužina                                     | 76 mm                                                                                                                                                                                                                                                                                                                              |
| Visina                                     | 54 mm                                                                                                                                                                                                                                                                                                                              |
| Širina                                     | 76 mm                                                                                                                                                                                                                                                                                                                              |
| Dubina                                     | 54 mm                                                                                                                                                                                                                                                                                                                              |
| Chemical and detergent products resistance | Otporan na alkohol (70%)<br>Otporan na alkohol (96%)<br>Otporan na A-mlečnu kiselinu<br>Otporan na razblaženi kvarterni amonijum<br>Otporan na razblaženo izbeljivač<br>Otporan na razblažen amonijak<br>Otporan na vodu sa sapunom<br>Otporan na čistač kristala<br>Otporan na vodonik peroksid 10 zapremina<br>Otporan na heksan |

### Okruženje

|                                     |                                             |
|-------------------------------------|---------------------------------------------|
| Oznake kvaliteta                    | AENOR<br>NF                                 |
| Ip stepen zaštite                   | IP55                                        |
| Ik stepen zaštite                   | IK08                                        |
| Otpornost na plamen                 | Samogasivo 650 °C u skladu sa IEC 60695-2-1 |
| Temperatura okoline za rad uređaja  | -5...40 °C                                  |
| Temperatura okoline za skladištenje | -25...55 °C                                 |

## Pakovanje

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 5,400 cm  |
| Package 1 Width              | 7,600 cm  |
| Package 1 Length             | 7,600 cm  |
| Package 1 Weight             | 70,000 g  |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 10        |
| Package 2 Height             | 9,000 cm  |
| Package 2 Width              | 17,000 cm |
| Package 2 Length             | 40,000 cm |
| Package 2 Weight             | 800,000 g |
| Unit Type of Package 3       | S04       |
| Number of Units in Package 3 | 60        |
| Package 3 Height             | 30,000 cm |
| Package 3 Width              | 40,000 cm |
| Package 3 Length             | 60,000 cm |
| Package 3 Weight             | 5,625 kg  |

## Održivost ponude

|                              |                                                                                                                                               |
|------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Status održive ponude        | Green Premium proizvod                                                                                                                        |
| Propis REACH                 |  <a href="#">REACH Deklaracija</a>                           |
| EU RoHS direktiva            | Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)                                                                  |
| Bez žive                     | Da                                                                                                                                            |
| Sustainable packaging        | Yes                                                                                                                                           |
| RoHS regulativa za Kinu      |  <a href="#">RoHS Deklaracija Za Kinu</a>                  |
| Informacije o RoHS izuzecima |  <a href="#">Da</a>                                        |
| Izjava o zaštiti okoliša     |  <a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a> |
| Profil cirkularnosti         | Nema potrebe za namenskim operacijama recikliranja                                                                                            |