

Tehničke karakteristike proizvoda

Karakteristike

MUR39913

Mureva Styl - nadgradna kutija - trostruka horizontalna - bela



Osnovne informacije

| | |
|--------------------------------|------------------|
| Grupa proizvoda | Mureva Styl |
| Tip proizvoda ili komponente | Nadgradna kutija |
| Kompatibilnost grupe proizvoda | orman |
| Nijansa boje | Bela (RAL 9003) |

Dopunske informacije

| | |
|--|---|
| Montaža uređaja | Nadgradno |
| Broj grupa | Trostruki horizontalno |
| Kablovski uvod | Jednostavan pristup ventilu |
| Uslovi upotrebe | U zatvorenom/na otvorenom |
| Materijal | PP (polipropilen) SEBS |
| Udaljenost između centara | 71 mm |
| Dužina | 218 mm |
| Visina | 54 mm |
| Širina | 76 mm |
| Dubina | 54 mm |
| Chemical and detergent products resistance | Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane |

Okruženje

| | |
|-------------------------------------|---|
| Oznake kvaliteta | AENOR NF |
| Ip stepen zaštite | IP55 |
| Ik stepen zaštite | IK08 |
| Otpornost na plamen | Samogasivo 650 °C u skladu sa IEC 60695-2-1 |
| Temperatura okoline za rad uređaja | -5...40 °C |
| Temperatura okoline za skladištenje | -25...55 °C |

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovdenavedenih informacija.

Packing Units

| | |
|-----------------------------|----------|
| Tip jedinice pakovanja 1 | PCE |
| Broj jedinica u pakovanju 1 | 1 |
| Pakovanje 1 težina | 171,9 g |
| Pakovanje 1 visina | 5,4 cm |
| Pakovanje 1 širina | 7,6 cm |
| Pakovanje 1 dužina | 21,8 cm |
| Tip jedinice pakovanja 2 | S04 |
| Broj jedinica u pakovanju 2 | 12 |
| Pakovanje 2 težina | 3,492 kg |
| Pakovanje 2 visina | 30 cm |
| Pakovanje 2 širina | 40 cm |
| Pakovanje 2 visina | 60 cm |
| Tip jedinice pakovanja 3 | BB1 |
| Broj jedinica u pakovanju 3 | 2 |
| Pakovanje 3 težina | 440 g |
| Pakovanje 3 visina | 16 cm |
| Pakovanje 3 širina | 8 cm |
| Pakovanje 3 visina | 40 cm |

Offer Sustainability

| | |
|------------------------------|--|
| Status održive ponude | Green Premium proizvod |
| Propis REACH | REACH Deklaracija |
| EU RoHS direktiva | Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija |
| Bez žive | Da |
| Informacije o RoHS izuzecima | Da |
| RoHS regulativa za Kinu | RoHS Deklaracija Za Kinu |
| Izjava o zaštiti okoliša | Profil Ekološke Prihvatljivosti Proizvoda |