

Tehničke karakteristike proizvoda

Karakteristike

NSYDBN1510

metalna industrijska kutija - niski poklopac -
V155xŠ105xD61 -IP55-siva RAL 7035



Osnovne informacije

Grupa proizvoda	Spacial SDB
Primena uređaja	Više namena
Tip proizvoda ili komponente	Spojna kutija
Tip ormana	Prazan orman
Tip prednjeg poklopca	Niski puni poklopac
Boja	Svetlosiva (RAL 7035)

Dopunske informacije

Nazivna visina ormana	155 mm
Nazivna širina ormana	105 mm
Nazivna dubina ormana	61 mm
Montaža ormana	Montaža na zid
Sastav uređaja	1 telo 1 poklopac 1 zavrtnj poklopca
Fiksiranje poklopca	Zavrtnj
Materijal	Čelik
Završna obrada	Epoksi poliester prah
Masa proizvoda	0,458 kg

Okruženje

Standardi	IEC 62208
IP stepen zaštite	IP55 u skladu sa IEC 60529
Ik stepen zaštite	IK07 conforming to IEC 62262

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,500 cm
Package 1 Width	11,000 cm
Package 1 Length	16,000 cm
Package 1 Weight	400,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	15,000 cm
Package 2 Width	34,000 cm
Package 2 Length	34,000 cm
Package 2 Weight	4,443 kg
Unit Type of Package 3	S04

Number of Units in Package 3	20
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	9,536 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja