

Tehničke karakteristike proizvoda

Karakteristike

NSYFB45

Spacial SM / Spacial SF nosač šine pod uglom od 45°



Osnovne informacije

Kategorie	Pribor za montažu
Tip proizvoda ili komponente	Nosač šine
Kompatibilnost grupe proizvoda	Spacial (Spacial SF) Spacial (Spacial SM) Spacial (Spacial SFM)
Anwendung	Više namena
Nennmaße des Gehäuses	-
Lokacija za montiranje	Na konstrukciji ormara
Namena proizvoda	Šina
Sastav uređaja	1 držač Elementi za montažu
Količina po setu	Set od 10
Materijal	Čelik

Dopunske informacije

Završna obrada	Obloženo cinkom
Visina	50 mm
Širina	70 mm
Dubina	220 mm

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,0 cm
Package 1 Width	4,5 cm
Package 1 Length	6,5 cm
Package 1 Weight	45,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6,5 cm
Package 2 Width	9,5 cm
Package 2 Length	11,0 cm
Package 2 Weight	450,0 g
Unit Type of Package 3	PAL
Number of Units in Package 3	200
Package 3 Height	20,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	9,0 kg

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovdenavedenih informacija.

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Informacije o RoHS izuzecima	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda

Ugovorna garancija

Garancija	18 meseci
-----------	-----------