

Tehničke karakteristike proizvoda

Karakteristike

NSYTBP191610H

ind. kutije IP66 IK08 U:V175Š150D100
S:H193Š164D105 neprovidan PC poklopac
V40



Osnovne informacije

Grupa proizvoda	Thalassa
Ime proizvoda	Thalassa TBP
Primena uređaja	Više namena
Category	Industrijska kutija
Visina	192 mm
Širina	164 mm
Dubina	105 mm
Unutrašnja visina	175 mm
Unutrašnja širina	150 mm
Unutrašnja dubina	100 mm
Montaža ormana	Montaža na zid
Sastav uređaja	1 telo 1 poklopac 4 zavrtnaj poklopca
Tip kućišta	Izliveno iz jednog dela
Tip prednjeg poklopca	Visoki puni poklopac
Fiksiranje poklopca	Plastični zavrtnji
Tip brave	Neodvojiv zavrtnaj ravan spoljašnja zaptivena oblast
Odvojni delovi	Poklopac sa neodvojivim zavrtnjima

Dopunske informacije

Materijal	Polikarbonat
Boja	Siva (RAL 7035)
Standardi	UL 508 A IEC 62208
Sertifikacija proizvoda	TÜV[RETURN]UL
Električna klasa izolacije	Klasa II
Lokacija montaže	Na otvorenom (sa nadstrešnicom ili zaklonom i antikondenzacionim ventilom)
Masa proizvoda	0,62 kg

Okruženje

Ip stepen zaštite	IP66 u skladu sa NEMA 4.4X
Ik stepen zaštite	IK08 conforming to IEC 62262
Otpornost na vatru	960 °C
Temperatura okoline za skladištenje	-15...60 °C
Operating temperature	-25...80 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12,45 cm
Package 1 Width	17,02 cm
Package 1 Length	21,08 cm
Package 1 Weight	1,24 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	17
Package 2 Height	40 cm
Package 2 Width	41 cm
Package 2 Length	61 cm
Package 2 Weight	10,94 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	425
Package 3 Height	215 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	287 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka

Ugovorna garancija

Garancija	18 meseci
-----------	-----------