

Tehničke karakteristike proizvoda

Karakteristike

NSYTBS191610H
ABS kutija IP66 IK07 RAL7035
U:V175Š150D100 S:H193Š164D105
neprovidni pokl. V40



Osnovne informacije

Grupa proizvoda	Thalassa
Ime proizvoda	Thalassa TBS
Primena uređaja	Više namena
Category	Industrijska kutija
Visina	193 mm
Širina	164 mm
Dubina	105 mm
Unutrašnja visina	175 mm
Unutrašnja širina	150 mm
Unutrašnja dubina	100 mm
Montaža ormara	Montaža na zid
Sastav uređaja	1 telo 1 poklopac 4 zavrtanj poklopca
Tip kućišta	Izliveno iz jednog dela
Tip prednjeg poklopca	Visoki puni poklopac
Fiksiranje poklopca	Plastični zavrtnji
Tip brave	Neodvojiv zavrtanj ravan spoljašnja zaptivena oblast
Odvojivi delovi	Poklopac sa neodvojivim zavrtnjima

Dopunske informacije

Materijal	ABS (akrilonitril-butadien-stiren)
Boja	Siva (RAL 7035)
Standardi	IEC 62208
Sertifikacija proizvoda	TÜV
Električna klasa izolacije	Klasa II
Ip stepen zaštite	IP66 u skladu sa NEMA 4.4X
Ik stepen zaštite	IK07 conforming to IEC 62262
Glow wire resistance	650 °C u skladu sa IEC 60695-2-11
Temperatura okoline za skladištenje	-15...40 °C
Operating temperature	-25...60 °C
Masa proizvoda	0,52 kg

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12 cm
Package 1 Width	17 cm
Package 1 Length	20,5 cm
Package 1 Weight	514 g
Unit Type of Package 2	CAR
Number of Units in Package 2	17

Package 2 Height	40 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10,06 kg
Unit Type of Package 3	P12
Number of Units in Package 3	204
Package 3 Height	136 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	125 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 months
-----------	-----------