

Tehničke karakteristike proizvoda

Karakteristike

NSYTBS342912T

ABS kutija IP66 IK07 RAL7035

U:V325Š275D120 S:V341Š291D128 providan
poklopac V20



Osnovne informacije

Grupa proizvoda	Thalassa
Ime proizvoda	Thalassa TBS
Primena uređaja	Više namena
Category	Industrijska kutija
Visina	341 mm
Širina	291 mm
Dubina	128 mm
Unutrašnja visina	325 mm
Unutrašnja širina	275 mm
Unutrašnja dubina	120 mm
Montaža ormana	Montaža na zid
Sastav uređaja	1 telo 1 poklopac 4 zavrtanj poklopca
Tip kućišta	Izliveno iz jednog dela
Tip prednjeg poklopca	Niski providni poklopac
Fiksiranje poklopca	Plastični zavrtnji
Tip brave	Neodvojiv zavrtanj ravan spoljašnja zaptivena oblast
Odvojivi delovi	Poklopac sa neodvojivim zavrtnjima

Dopunske informacije

Materijal	ABS (akrilonitril-butadien-stiren)
Boja	Siva (RAL 7035) Providna
Standardi	IEC 62208
Sertifikacija proizvoda	TÜV
Električna klasa izolacije	Klasa II
Ip stepen zaštite	IP66 u skladu sa NEMA 4.4X
Ik stepen zaštite	IK07 conforming to IEC 62262
Glow wire resistance	650 °C u skladu sa IEC 60695-2-11
Temperatura okoline za skladištenje	-15...40 °C
Operating temperature	-25...60 °C
Masa proizvoda	1,448 kg

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14,0 cm
Package 1 Width	30,0 cm
Package 1 Length	35,5 cm
Package 1 Weight	1,46 kg
Unit Type of Package 2	CAR

Number of Units in Package 2	4
Package 2 Height	40,0 cm
Package 2 Width	40,0 cm
Package 2 Length	60,0 cm
Package 2 Weight	7,1 kg
Unit Type of Package 3	P12
Number of Units in Package 3	48
Package 3 Height	120 cm
Package 3 Width	80 cm
Package 3 Length	136 cm
Package 3 Weight	88 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------