

Tehničke karakteristike proizvoda

Karakteristike

NU174418

Ugradna kutija 4 kolone bela



Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	Radna stanica
Broj modula	4 x 4 modules
Pozicija montiranja ručice	Vertikalno
Način pričvršćivanja	Embedment Kukicama

Dopunske informacije

Zaštitna oprema	Ram Montažni ram
Montaža uređaja	Ugradno
Kablovski uvod	4 dno cable entries 50 x 35 mm for size 25 mm for diameter 8 definisani otvori 20 mm for diameter 8 definisani otvori 25 mm for diameter 4 dno cable entries 50 x 35 mm for size 20 mm for diameter
Otpornost na vatru	850 °C, vreme gašenja <30 sekundi
Materijal	ABS (akrilonitril-butadien-stiren): separator PC: kutija ABS (akrilonitril-butadien-stiren): dekorativni ram
Dubina	62 mm
Širina	300 mm
Visina	165 mm
Masa proizvoda	0,514 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Ik stepen zaštite	IK04
-------------------	------

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,0 cm
Package 1 Width	18,5 cm
Package 1 Length	31,5 cm
Package 1 Weight	656,0 g

Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	30,0 cm
Package 2 Width	40,0 cm
Package 2 Length	60,0 cm
Package 2 Weight	7,302 kg
Unit Type of Package 3	P06
Number of Units in Package 3	40
Package 3 Height	77,0 cm
Package 3 Width	80,0 cm
Package 3 Length	60,0 cm
Package 3 Weight	37,708 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH free of SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Toxic heavy metal free	Da
Mercury free	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
RoHS exemption information	Da
Izjava o zaštiti životne sredine	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Minimum percentage of recycled plastic content	23