

Tehničke karakteristike proizvoda

Karakteristike

NU200130

1 modul uzani ram aluminijum



Osnovne informacije

Grupa proizvoda	New Unica
Primena uređaja	Montaža
Tip proizvoda ili komponente	Dekorativni ram
Ime dekorativnog elementa	Unica
Broj dvostrukih modula	Jednostruki
Pravac instalacije	Horizontalno
Tip prekidača	Pojedinačno
Broj modula	1 modul
Način pričvršćivanja	Utično
Nijansa boje	Aluminijum

Dopunske informacije

Zaštitna oprema	Montažni ram
Materijal	Termoplastika ABS-UV stabilizovana: dekorativni ram PBT (polibutilen-tereftalat): montažni ram
Standardi	IEC 60884-1 IEC 60669-1
Širina	36 mm
Visina	75 mm
Dubina	9 mm
Masa proizvoda	0,011 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Ik stepen zaštite	IK04
Ip stepen zaštite	IP21 D

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,5 cm
Package 1 Width	3,5 cm
Package 1 Length	7,5 cm
Package 1 Weight	14,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6,5 cm

Package 2 Width	12,5 cm
Package 2 Length	18,5 cm
Package 2 Weight	198,0 g
Unit Type of Package 3	S01
Number of Units in Package 3	40
Package 3 Height	15,0 cm
Package 3 Width	15,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	1,006 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH free of SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Toxic heavy metal free	Da
Mercury free	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
RoHS exemption information	Da
Izjava o zaštiti životne sredine	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Minimum percentage of recycled plastic content	34