

# Tehničke karakteristike proizvoda

## Karakteristike

# NU280611

## Ram 3E Unica Studio jabuka zeleno/beli



### Osnovne informacije

Grupa proizvoda	New Unica
Primena uređaja	Montaža
Tip proizvoda ili komponente	Dekoratívni ram
Ime dekorativnog elementa	Unica Studio Color
Broj dvostrukih modula	Trostruki
Pravac instalacije	Horizontalno vertikalno
Tip prekidača	Triple
Broj modula	3 x 2 modules
Način pričvršćivanja	Utično
Nijansa boje	Light green
Side color	Bela (RAL 9003)

### Dopunske informacije

Materijal	Termoplastika ABS-UV stabilizovana: dekorativni ram Polikarbonat: međuploča
Standardi	IEC 60669-1 IEC 60884-1
Širina	227 mm
Visina	85 mm
Dubina	10 mm
Masa proizvoda	0,047 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

### Okruženje

Ik stepen zaštite	IK04
Ip stepen zaštite	IP21 D

### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,0 cm
Package 1 Width	8,5 cm
Package 1 Length	22,7 cm
Package 1 Weight	50,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	6,0 cm

Package 2 Width	11,0 cm
Package 2 Length	25,0 cm
Package 2 Weight	311,0 g
Unit Type of Package 3	S03
Number of Units in Package 3	85
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	5,723 kg

## Održivost ponude

EU RoHS direktiva	Nije primenljivo, izvan zakonskog okvira direktive EU RoHS
-------------------	------------------------------------------------------------