

Osnovne informacije

Grupa proizvoda	New Unica
Primena uređaja	Upravljanje
Tip proizvoda ili komponente	Roller blind switch
Prezentacija uređaja	Mehanizam sa centralnom pločom
Nazivna struja	10 AX
[ue] nazivni napon	250 V
Tip mreže	AC
Mrežna frekvencija	50/60 Hz
Način pričvršćivanja	Utično
Nijansa boje	Bela (RAL 9003)
Nijansa boje	Bela

Dopunske informacije

Montaža uređaja	Ugradno
Broj modula	1 modul
Vrsta tehnologije	Elektromehanička
Izvršni organ	Preklopni prekidač
Broj prekidača	2
Funkcija prekidača	Jednopolni naizmenični
Primena prekidača	Roletne
Broj polova	1
Tip kontakata i sastav	1 C/O
Mehanička blokada	Blokada između funkcija nagore/nadole
Nazivna struja prekida	2,5 A za motor
Udaljenost otvaranja	> 3 mm
Signalna lampica	Bez LED
Označavanje	Nadole UP
Povezivanje - priključci	Vijčani priključci
Poprečni presek kabla	2,5 Mm ² fleksibilni kabl 1,5...2,5 Mm ² fleksibilni kabl 2,5 Mm ² kruti kabl 1,5...2,5 mm ² kruti kabl
Minimalna moć isključenja opterećenja	200 operacija 1.25 In i 1.1 Un, cos phi = 0,3
Električna trajnost	10000 ciklusa, cos phi = 0,6
Otpornost izolacije	> 5 MOhm pri 500 V
Dielektrična snaga	2000 V
Materijal	ASA + PC: mehanizam poklopca ABS (akrilonitril-butadien-stiren): mehanizam poklopca
Standardi	LV direktiva EMC direktiva EN 60669-1
Sertifikacija proizvoda	ISI[RETURN]CE
Temperatura okoline za rad uređaja	-5...40 °C
Temperatura okoline za skladištenje	-5...40 °C
Dubina za ugradnju	31,5 mm

Dubina	40,6 mm
Širina	22,5 mm
Visina	45 mm
Masa proizvoda	0,036 kg





Okruženje

Ik stepen zaštite	IK04
Ip stepen zaštite	IP4X
Karakteristike životne sredine	Tečnost za čišćenje prozora Tečni sapun Aceton UV otpornost Ulje Izbeljivač Benzin Alkohol

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,300 cm
Package 1 Width	4,000 cm
Package 1 Length	4,500 cm
Package 1 Weight	25,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6,500 cm
Package 2 Width	12,300 cm
Package 2 Length	18,600 cm
Package 2 Weight	304,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	360
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	11,594 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja