

## Tehničke karakteristike proizvoda

### Karakteristike

# NU342818

## USB 2.0 utičnica napajanja 1 mod bela



### Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	USB punjač
Prezentacija uređaja	Mehanizam

### Dopunske informacije

Primena uređaja	Punjač
Montaža uređaja	Ugradno
Broj modula	1 modul
Type of USB power supply	USB type A
Nijansa boje	Bela (RAL 9003)
Završna obrada	Sjajno
[ue] nazivni napon	100...240 V AC 50/60 Hz
Nazivna izlazna snaga	5 W
Ulazna snaga	7,5 W
Broj utičnica	1
Integrisani načini povezivanja	1 USB tip A 5 V DC, maksimalna struja opterećenja: 1 A
Materijal	PC (polikarbonat) GF10 FR: kućište PC (polikarbonat) GF10 FR: unutrašnji poklopac Termoplastika ABS-UV stabilizovana: centralna pločica
Tip zaštite	Zaštita od kratkog spoja
Broj priključaka	2 vijčani priključci
Oblik glave zavrtnja	Pozidriv No 1
Kapacitet priključaka	1.5...2.5 mm <sup>2</sup> za kruti kabl(ovi) 1.5...2.5 mm <sup>2</sup> za fleksibilni kabl(ovi)
Dužina ogoljenog dela žice	8 mm
Kompatibilnost proizvoda	Svi uređaji koji ispunjavaju EN 62684 standard
Način pričvršćivanja	Utično
Tip pakovanja	Pakovanje u kesicama
Temperatura okoline za rad uređaja	5...45 °C
Temperatura okoline za skladištenje	-5...50 °C
Standardi	IEC 62368-1 EN 61000-6-1 EN 61000-6-3 IEC 62680-3
Visina	45 mm
Širina	22,5 mm
Dubina	42 mm
Dubina za ugradnju	30,8 mm

Masa proizvoda	0,03 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

## Okruženje

Električna klasa izolacije	Klasa II
Ik stepen zaštite	IK04
Ip stepen zaštite	IP2XC

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,2 cm
Package 1 Width	4,3 cm
Package 1 Length	4,5 cm
Package 1 Weight	32,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5,8 cm
Package 2 Width	14,3 cm
Package 2 Length	26,0 cm
Package 2 Weight	394,0 g
Unit Type of Package 3	S02
Number of Units in Package 3	50
Package 3 Height	15,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	2,287 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	<a href="#">REACh Deklaracija</a>
REACh bez SVHC	Da
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	<a href="#">Informacije O Kraju Radnog Veka</a>
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.