

Tehničke karakteristike proizvoda

Karakteristike

XVBC8B8

žuti trepćući blok 24V 10J + opcije



Osnovne informacije

Grupa proizvoda	Harmony XVB Universal
Tip proizvoda ili komponente	Svetleća kolona
Tip baze svetleće kolone ili semafora	Svetleća jedinica
Tip signalizacije	Treperenje
Prečnik za montiranje	70 mm
Ime komponente	XVBC
Materijal	Polikarbonat
Svetlosni izvor	Integrisana svetiljka za snažni bljesak, žuta
Tip sijalice	Svetiljka za snažan bljesak
[us] nazivni napon	24 V AC/DC
Energija bljeska	10 J

Dopunske informacije

Način spajanja	Za sastavljanje kod korisnika, do 5 jedinica
Povezivanje - priključci	Vijčani priključni blokovi, $\leq 1 \times 1.5 \text{ mm}^2$ sa kablovskim završetkom
[ui] nazivni napon izolacije	250 V u skladu sa IEC 60947-1
Nazivno ograničenje napona	$0.85 \dots 1.1 U_n$ u skladu sa IEC 60947-5-1
Potrošnja struje	$< 1300 \text{ mA AC}$ $< 850 \text{ mA DC}$
[uimp] nazivni podnosivi impulsni napon	4 kV u skladu sa IEC 60947-1
Frekvencija treptanja	1 Hz
Cad ukupna širina	70 mm
Cad ukupna visina	157 mm
Cad ukupna dubina	70 mm
Masa proizvoda	0,305 kg

Okruženje

Sertifikacija proizvoda	CCC[RETURN]EAC[RETURN]CSA C22-2 No 14[RETURN]UL 508
Standardi	EN/IEC 60947-5-1
Tretman zaštite	TC
Temperatura okoline za skladištenje	$-40 \dots 70 \text{ }^\circ\text{C}$
Klasa zaštite protiv električnog udara	Klasa I na cevnom nosaču u skladu sa IEC 61140 Klasa II na bazi u skladu sa IEC 61140
Ip stepen zaštite	IP65 na bazi za fiksiranje XVBZ0. u skladu sa IEC 60529 IP66 na bazi u skladu sa IEC 60529
Nema stepen zaštite	Type 4X u skladu sa UL (u zatvorenom)

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18,700 cm
Package 1 Width	8,000 cm
Package 1 Length	8,000 cm

Package 1 Weight	324,000 g
Unit Type of Package 2	S03
Number of Units in Package 2	18
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	6,291 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.


Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Indicator Bank with “Flash” Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit XVBC***, to be ordered separately
- (3) “Flash” unit

Number of illuminated or audible signalling units other than “flash” tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06