

# Tehničke karakteristike proizvoda

## Karakteristike

## ZCKD08

glava graničnog prekidača ZCKD - šipka sa oprugom





## Osnovne informacije

Grupa proizvoda	Telemecanique granični prekidači XC Standard
Ime serije	Standardni format
Tip proizvoda ili komponente	Glava graničnog prekidača
Kratko ime uređaja	ZCKD
Tip glave	Glava za više smerova
Kompatibilnost proizvoda	XCKL XCKM XCKS

Pridruženo telo	ZCKM7H7 ZCKS1H29 ZCKM8H7 ZCKMD31 ZCKSD37 ZCKS5 ZCKS9 ZCKMD31H7 ZCKS6 ZCKL6H7 ZCKSD35H29 ZCKSD39H29 ZCKMD37 ZCKM6H7 ZCKSD37H29 ZCKSD31H29 ZCKMD39H7 ZCKS1 ZCKMD39H29 ZCKM7 ZCKSD35 ZCKM7H29 ZCKLD39 ZCKS2 ZCKS7H29 ZCKLD31 ZCKL1H7 ZCKM5H29 ZCKM9H29 ZCKMD39 ZCKM1 ZCKL5 ZCKM5 ZCKMD35 ZCKM1H29 ZCKLD35 ZCKL1 ZCKS5H29 ZCKMD31H29 ZCKM5H7 ZCKSD31 ZCKLD39H7 ZCKLD37 ZCKM6 ZCKL6 ZCKSD39 ZCKM8 ZCKS9H29 ZCKL8H7 ZCKS8H29 ZCKMD35H29 ZCKM1H7 ZCKL7 ZCKMD37H29 ZCKLD37H7 ZCKLD35H7 ZCKL8 ZCKMD37H7 ZCKL5H7 ZCKL7H7 ZCKS7 ZCKS8 ZCKMD35H7 ZCKM9 ZCKS6H29 ZCKS2H29 ZCKLD31H7 ZCKM6H29 ZCKM8H29
Kretanje glave	Više smerova Obrtno
Tip glave uredaja	Šipka sa oprugom sa povratkom
Tip prilaza	Prilaz sa više strana

## Dopunske informacije

Aktiviranje prekidača	Sa bilo kojim pokretnim delom
Pozitivno otvaranje	Bez
Materijal glave	Metal





## Okruženje

Temperatura okoline za rad uređaja	-25...70 °C
Temperatura okoline za skladištenje	-40...70 °C
Karakteristike životne sredine	Standardna sredina

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,6 cm
Package 1 Width	3,6 cm
Package 1 Length	15,8 cm
Package 1 Weight	42 g
Unit Type of Package 2	S01
Number of Units in Package 2	18
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1,1 kg
Unit Type of Package 3	P06
Number of Units in Package 3	288
Package 3 Height	45 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	24,772 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 <a href="#">REACH Deklaracija</a>
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  <a href="#">EU RoHS deklaracija</a>
Bez žive	Da
Informacije o RoHS izuzecima	 <a href="#">Da</a>
Izjava o zaštiti okoliša	 <a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>

## Ugovorna garancija

Garancija	18 months
-----------	-----------