



# Tehničke karakteristike proizvoda Karakteristike

## 31111 rastavljač Compact INS400 - 400 A - 4P



### Osnovne informacije

Grupa proizvoda	Compact
Tip proizvoda ili komponente	Rastavljač
Ime proizvoda	Compact INS
Broj polova	4P
Tip mreže	DC AC
Mrežna frekvencija	50/60 Hz
[ie] nazivna struja	AC-22A: 400 A AC 50/60 Hz 220/240 V AC-22A: 400 A AC 50/60 Hz 380/415 V AC-22A: 400 A AC 50/60 Hz 440/480 V AC-22A: 400 A AC 50/60 Hz 480 V NEMA AC-22A: 400 A AC 50/60 Hz 500/525 V AC-22A: 400 A AC 50/60 Hz 660/690 V AC-23A: 400 A AC 50/60 Hz 220/240 V AC-23A: 400 A AC 50/60 Hz 380/415 V AC-23A: 400 A AC 50/60 Hz 440/480 V AC-23A: 400 A AC 50/60 Hz 480 V NEMA AC-23A: 400 A AC 50/60 Hz 500/525 V AC-23A: 400 A AC 50/60 Hz 660/690 V DC-22A: 400 A DC 125 V 2 pola serijski DC-22A: 400 A DC 250 V 4 pola serijski DC-23A: 400 A DC 125 V 2 pola serijski DC-23A: 400 A DC 250 V 4 pola serijski
[ui] nazivni napon izolacije	800 V AC 50/60 Hz
[uimp] nazivni podnosivi impulsni napon	8 KV 8 kV u skladu sa IEC 60947-3
[ith] dozvoljena termička struja u vazduhu	400 A pri 60 °C
[icm] nazivna kratkospojna moć uključanja	330 KA sa zaštitnim prekidačem 690 V AC pri 50/60 Hz 50 kA sam rastavljač 690 V AC pri 50/60 Hz
[ue] nazivni napon	250 V DC 690 V AC 50/60 Hz
Pogodno za izolaciju	Da
Indikator pozicije kontakta	Da
Vidljivo prekidanje	Ne
Stepen zaprljanosti	3

### Dopunske informacije

Tip upravljanja	Direktno prednjom zakretnom ručicom
Boja drške	Crna
Način montiranja	Fiksno
Nosači za montažu	Šina Ploča
Gornji priključak	Prednja
Donji priključak	Prednji

Maksimalna snaga	AC-23: 110 kW pri 220/240 V AC 50/60 Hz AC-23: 110 kW pri 230 V AC 50/60 Hz (NEMA) AC-23: 200 kW pri 380/415 V AC 50/60 Hz AC-23: 220 kW pri 440 V AC 50/60 Hz AC-23: 220 kW pri 480 V AC 50/60 Hz (NEMA) AC-23: 250 kW pri 500/525 V AC 50/60 Hz AC-23: 400 kW pri 660/690 V AC 50/60 Hz
Nazivni ciklus	Neprekidno
[icw] kratkotrajna podnosiva struja kratkog spoja	11,5 KA tokom 3 s u skladu sa IEC 60947-3 20 KA tokom 1 s u skladu sa IEC 60947-3 4 KA tokom 30 s u skladu sa IEC 60947-3 4,9 kA tokom 20 s u skladu sa IEC 60947-3
Mehanička trajnost	10000 ciklusa
Električna trajnost	AC-22A: 1500 ciklusa 440 V AC 50/60 Hz AC-22A: 1500 ciklusa 500 V AC 50/60 Hz AC-22A: 1500 ciklusa 690 V AC 50/60 Hz AC-23A: 1500 ciklusa 440 V AC 50/60 Hz AC-23A: 1500 ciklusa 500 V AC 50/60 Hz AC-23A: 1500 ciklusa 690 V AC 50/60 Hz DC-23A: 1000 ciklusa 250 V DC 4 pola serijski
Povezivanje	45 mm
Visina	205 mm
Širina	185 mm
Dubina	120 mm
Masa proizvoda	4,9 kg

## Okruženje

Standardi	IEC 60947-1 IEC 60947-3
Sertifikacija proizvoda	KEMA-KEUR[RETURN]CCC
Ip stepen zaštite	IP40 conforming to IEC 60529
Ik stepen zaštite	IK07 conforming to EN 50102
Temperatura okoline za rad uređaja	-25...70 °C
Temperatura okoline za skladištenje	-50...85 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18,800 cm
Package 1 Width	19,400 cm
Package 1 Length	22,400 cm
Package 1 Weight	5,538 kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30,000 cm
Package 2 Width	40,000 cm
Package 2 Length	60,000 cm
Package 2 Weight	22,918 kg
Unit Type of Package 3	P12
Number of Units in Package 3	16
Package 3 Height	50,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	100,000 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
EU RoHS direktiva	U skladu sa izuzecima
Bez žive	Da
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti životne sredine	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	<a href="#">Informacije O Kraju Radnog Veka</a>
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

## Ugovorna garancija

Garancija	18 meseci
-----------	-----------