



Tehničke karakteristike proizvoda Karakteristike

33813 naponski okidač MX - 200..250 V DC/AC 50/60 Hz

Osnovne informacije

Grupa proizvoda	MasterPacT
Grupa proizvoda	Masterpact NT ComPacT NS630b...1600 new generation
Kratko ime uređaja	MX
Tip proizvoda ili komponente	Naponski okidač
Primena uređaja	Upravljanje
Tip naponskog okidača	Kalem za isključenje Trenutni naponski okidač
Tip upravljanja	Standardni
Napon upravljačkog kola	200...250 V AC 50/60 Hz 200...250 V DC
Circuit breaker mounting mode	Izvlačivo
Kompatibilnost grupe proizvoda	Masterpact Masterpact NT Compact Compact NS630b...1600

Dopunske informacije

Operating threshold	0.7...1.1 x Un otvaranje
Vreme odziva	50 ms +/- 10 % za Masterpact NT 50 ms +/- 10 % za Compact NS630b...1600
Snaga držanja	4.5 VA

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,000 cm
Package 1 Width	6,000 cm
Package 1 Length	8,500 cm
Package 1 Weight	180,300 g
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Height	15,000 cm
Package 2 Width	15,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	2,003 kg
Unit Type of Package 3	P12
Number of Units in Package 3	320
Package 3 Height	45,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	76,096 kg

Održivost ponude

Pakovanje bez plastike	Da
Pakovanje sa recikliranim kartonom	Da
SCIP broj	Ad764790-535b-4a4e-825e-50fd804b5824
Uredba REACH	REACH Deklaracija
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće
Performanse sadržaja halogena	Proizvod sadrži halogen iznad dozvoljenog nivoa
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	3

Ugovorna garancija

Garancija	18 meseci
-----------	-----------