



Tehničke karakteristike proizvoda

Karakteristike

81139

Mureva utičnica-siva- 2P+E -10/16A - 250V- italijanski stand.- IP65-nadgradna

Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Utičnica
Kratko ime uređaja	Mureva socket
Kategorija priključnice i utikača	Niskonaponska
Broj polova	2P + E
Tip mreže	AC
Standard utičnice	Za domaćinstvo Italijanski

Dopunske informacije

[in] nazivna struja	16 A 10 A
Mrežna frekvencija	50/60 Hz
[ue] nazivni napon	250 V
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Pinovi: nerđajući čelik Opruge: nerđajući čelik
Tip poklopca	Poklopac
Montaža uređaja	Nadgradno
Način montiranja	Montaža na panel
Broj utičnica	2
Povezivanje - priključci	Neodvojni zavrtnji
Masa proizvoda	0,13 kg
Dimenzija baze	65 x 85 mm
Visina	85 mm
Širina	65 mm
Dubina	45,2 mm
Boja	Siva (RAL 7035)

Okruženje

Standardi	IEC 60884
Ip stepen zaštite	IP65 conforming to IEC 60529
Ik stepen zaštite	IK09 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-1
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Temperatura okoline za rad	35 °C 86400 s) -25...40 °C

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova poveznica ili zavisna društva neće snositi odgovornost za zloupotrebu ovde navedenih informacija.

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20,000 cm
Package 1 Width	5,000 cm
Package 1 Length	5,000 cm
Package 1 Weight	131,400 g
Unit Type of Package 2	BB1
Number of Units in Package 2	18
Package 2 Height	12,200 cm
Package 2 Width	26,900 cm
Package 2 Length	27,100 cm
Package 2 Weight	2,365 kg
Unit Type of Package 3	S03
Number of Units in Package 3	54
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	7,250 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
SCIP broj	52b60409-d705-46c7-9ba3-cc3ef6e307da
Uredba REACH	REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	6

Ugovorna garancija

Garancija	18 months
-----------	-----------