



Tehničke karakteristike proizvoda

Karakteristike

81142

RJ 45 utičnica 65 x 85 - sa 1 adapterom RJ45 Infra+ - IP65

Osnovne informacije

Grupa proizvoda	PratiKa
Tip proizvoda ili komponente	Nosač
Kratko ime uređaja	RJ45 modul
Kategorija priključnice i utikača	Niskonaponska
Standard utičnice	Za domaćinstvo

Dopunske informacije

Materijal utikača, utičnice	Kućište: samogasivi polimer
Tip poklopca	Poklopac
Montaža uređaja	Nadgradno
Način montiranja	Montaža na panel
Povezivanje - priključci	Neodvojivi zavrtnji
Masa proizvoda	0,084 kg
Dimenzija baze	65 x 85 mm
Visina	85 mm
Širina	65 mm
Dubina	45,2 mm
Boja	Siva (RAL 7035)

Okruženje

Standardi	IEC 60309-2 IEC 60309-1
Ip stepen zaštite	IP65 conforming to IEC 60529
Ik stepen zaštite	IK09 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Temperatura okoline za rad	35 °C 86400 s) -25...40 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,5 cm
Package 1 Width	8,5 cm
Package 1 Length	6,5 cm
Package 1 Weight	84,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	18

Package 2 Height	12,0 cm
Package 2 Width	21,0 cm
Package 2 Length	27,0 cm
Package 2 Weight	1,659 kg
Unit Type of Package 3	S03
Number of Units in Package 3	54
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	5,464 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Ne
Uredba REACH	REACH Deklaracija
Bez SVHC-a REACH	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	1

Ugovorna garancija

Garancija	18 months
-----------	-----------