



# Tehničke karakteristike proizvoda Karakteristike

## 81199

### Mureva socket - for container - 32 A - 3P+E - 400...440 V AC - IP 67

#### Osnovne informacije

Grupa proizvoda	PratiKa
Tip proizvoda ili komponente	Utičnica za kontejner
Kratko ime uređaja	PratiKa utičnica
Kategorija priključnice i utikača	Niskonaponska
Tip industrijske priključnice	Vijčana
Broj polova	3P + E
Tip mreže	AC
Standard utičnice	Industrijski

#### Dopunske informacije

Način montiranja	Nadzidno
Kategorija priključnice i utikača	Pod uglom
[in] nazivna struja	32 A
[ue] nazivni napon	400...440 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	3 h
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Priključci: poniklovan mesing
Povezivanje - priključci	Neodvojivi zavrtnji, potpuno olabavljeni
Poprečni presek kabla	2,5...10 mm <sup>2</sup>
Kablovski uvod	Kablovska uvodnica
Tip navoja	Pg 21
Masa proizvoda	0,5 kg
Boja	Crvena

#### Okruženje

Standardi	EN 60309-2 EN 60309-1
Ip stepen zaštite	IP67 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-1
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Temperatura okoline za rad	35 °C 86400 s )

#### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,05 cm
Package 1 Width	4,6 cm
Package 1 Length	15,0 cm

Package 1 Weight	564,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Height	11,0 cm
Package 2 Width	21,0 cm
Package 2 Length	27,0 cm
Package 2 Weight	1,128 kg
Unit Type of Package 3	S03
Number of Units in Package 3	6
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	3,658 kg

### Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
SCIP broj	89350e0d-a4ac-4516-bf86-fdaed8a227fc
Uredba REACH	<a href="#">REACH Deklaracija</a>
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No

### Ugovorna garancija

Garancija	18 meseci
-----------	-----------