



# Tehničke karakteristike proizvoda Karakteristike

## 81383

### Mureva Wander utikač - ravni - 63 A - 3P + N + E - 380...415 V AC - IP67

#### Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Wander utikač
Kratko ime uređaja	Mureva plug
Kategorija priključnice i utikača	Niskonaponska
Broj polova	3P + N + E
Tip mreže	AC
Standard utičnice	Industrijski

#### Dopunske informacije

Kategorija priključnice i utikača	Ravna
[in] nazivna struja	63 A
[ue] nazivni napon	380...415 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	6 h
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Pinovi: poniklovan mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Poprečni presek kabla	6...25 mm <sup>2</sup>
Spoljašnji prečnik kabla	17...31 mm
Kablovski uvod	Kablovska uvodnica
Tip navoja	Pg 36
Masa proizvoda	0,792 kg
Visina	265 mm
Širina	110 mm
Dubina	110 mm
Boja	Siva (RAL 7035)
Boja poklopca	Crvena

#### Okruženje

Standardi	IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP67 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Nadmorska visina za rad	2000 m
Temperatura okoline za rad	35 °C 86400 s ) -25...40 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11,300 cm
Package 1 Width	11,300 cm
Package 1 Length	26,400 cm
Package 1 Weight	802,000 g
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	8,507 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	50,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	80,056 kg

## Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Ne
SCIP broj	661ec80b-b956-4b0a-92bb-53046f4cfb4c
Uredba REACh	<a href="#">REACh Deklaracija</a>
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti okoline	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	25

## Ugovorna garancija

Garancija	18 meseci
-----------	-----------