



# Tehničke karakteristike proizvoda

## Karakteristike

# 81894

## Mureva utikač - ravni - 125A - 3P + E - 380...415 V AC - IP67 - panel

### Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Utičnica
Kratko ime uređaja	utikač za montažu na panel
Kategorija priključnice i utikača	Niskonaponska
Broj polova	3P + E
Tip mreže	AC
Standard utičnice	Industrijski

### Dopunske informacije

Način montiranja	Montaža na panel
Kategorija priključnice i utikača	Ravna
[in] nazivna struja	125 A
[ue] nazivni napon	380...415 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	6 h
Materijal utikača, utičnice	Kućište: samogasivi polimer
Materijal kontakta	Pinovi: poniklovan mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Poprečni presek kabla	16...70 mm <sup>2</sup>
Tip navoja	Pg 48
Masa proizvoda	1,5 kg
Dimenzija baze	110 x 114 mm
Visina	325 mm
Širina	131 mm
Dubina	131 mm
Boja	Siva (RAL 7035)
Boja poklopca	Crvena

### Okruženje

Standardi	IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP67 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Nadmorska visina za rad	2000 m
Temperatura okoline za rad	35 °C 86400 s ) -25...40 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11,000 cm
Package 1 Width	11,500 cm
Package 1 Length	14,000 cm
Package 1 Weight	997,000 g
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	10,374 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	45,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	94,992 kg

## Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
SCIP broj	E57d0e16-20fd-447f-8324-ed3dc27095fd
Uredba REACH	<a href="#">REACH Deklaracija</a>
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti okoline	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	9