



Tehničke karakteristike proizvoda

Karakteristike

82301

Mureva Wander utikač - ravni - 16 A - 2P - 20...25 V AC - IP44

Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Wander utikač
Kratko ime uređaja	Mureva plug
Kategorija priključnice i utikača	Veoma nizak napon
Broj polova	2P
Tip mreže	AC
Standard utičnice	Industrijski

Dopunske informacije

Kategorija priključnice i utikača	Ravna
[in] nazivna struja	16 A
[ue] nazivni napon	20...25 V
Mrežna frekvencija	50/60 Hz
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Pinovi: poniklovan mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Poprečni presek kabla	4...10 mm ²
Spoljašnji prečnik kabla	6...23 mm
Kablovski uvod	Kablovska uvodnica
Tip navoja	Pg 21
Masa proizvoda	0,141 kg
Visina	158 mm
Širina	57,5 mm
Dubina	57,5 mm
Boja	Siva (RAL 7035)
Boja poklopca	Ljubičasta

Okruženje

Standardi	IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP44 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Nadmorska visina za rad	2000 m
Temperatura okoline za rad	35 °C 86400 s) -25...40 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,0 cm
Package 1 Width	6,0 cm
Package 1 Length	15,9 cm
Package 1 Weight	131,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,0 cm
Package 2 Width	26,8 cm
Package 2 Length	27,0 cm
Package 2 Weight	1,434 kg
Unit Type of Package 3	S03
Number of Units in Package 3	40
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	6,224 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
SCIP broj	661ec80b-b956-4b0a-92bb-53046f4cfb4c
Uredba REACh	REACh Deklaracija
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	3

Ugovorna garancija

Garancija	18 meseci
-----------	-----------