



Tehničke karakteristike proizvoda

Karakteristike

83042

Unika utičnica sa blokadom - 32 A - 2P + E - 200...250 V AC - IP44 - nadzidna

Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Blokada utičnice
Kratko ime uređaja	Mureva socket
Kategorija priključnice i utikača	Niskonaponska
Broj polova	2P + E
Tip mreže	AC
Standard utičnice	Industrijski

Dopunske informacije

Način montiranja	Nadzidno
[in] nazivna struja	32 A
[ue] nazivni napon	200...250 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	6 h
Tip zaštite	Bez zaštite
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Priključci: poniklovan mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Maksimalni poprečni presek kabla	10 mm ²
Maksimalni spoljašnji prečnik kabla	25 mm
Kablovski uvod	Kablovska uvodnica
Tip navoja	Pg 21
Masa proizvoda	1,003 kg
Dimenzija baze	103 x 255 mm
Visina	255 mm
Širina	103 mm
Dubina	151 mm
Boja	Siva (RAL 7035)
Boja poklopca	Plava

Okruženje

Standardi	IEC 60309-2 IEC 60309-1
Ip stepen zaštite	IP44 conforming to IEC 60529
Ik stepen zaštite	IK09 conforming to EN 62262
Otpornost na vatru	750 °C u skladu sa IEC 60695-2-11
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Temperatura okoline za rad	35 °C 86400 s) -25...40 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10,500 cm
Package 1 Width	17,000 cm
Package 1 Length	26,000 cm
Package 1 Weight	1,070 kg
Unit Type of Package 2	S03
Number of Units in Package 2	5
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	5,860 kg
Unit Type of Package 3	P12
Number of Units in Package 3	40
Package 3 Height	50,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	58,616 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
SCIP broj	70ff4a45-7b66-43af-a141-7990e6438899
Uredba REACH	REACH Deklaracija
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	128
Minimalni procenat recikliranog	58

Ugovorna garancija

Garancija	18 meseci
-----------	-----------