



Tehničke karakteristike proizvoda

Karakteristike

83156

Mureva industrijska utičnica - 16 A - 3P + N + E - 200...250 V AC - IP67

Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Utičnica
Kratko ime uređaja	Mureva socket
Kategorija priključnice i utikača	Niskonaponska
Broj polova	3P + N + E
Tip mreže	AC
Standard utičnice	Industrijski

Dopunske informacije

Način montiranja	Nadzidno
Kategorija priključnice i utikača	Pod uglom
[in] nazivna struja	16 A
[ue] nazivni napon	200...250 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	9 h
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Pinovi: nerđajući čelik Priključci: poniklovan mesing Opruge: nerđajući čelik
Povezivanje - priključci	Neodvojni zavrtnji, potpuno olabavljeni
Poprečni presek kabla	1...4 mm ²
Spoljašnji prečnik kabla	8...15 mm
Kablovski uvod	Kablovska uvodnica
Tip navoja	Pg 21
Masa proizvoda	0,493 kg
Dimenzija baze	106 x 130 mm
Visina	178 mm
Širina	106 mm
Dubina	143 mm
Boja	Siva (RAL 7035)
Boja poklopca	Plava

Okruženje

Standardi	EN 60309-2 EN 60309-1
Ip stepen zaštite	IP67 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Temperatura okoline za rad	35 °C 86400 s)

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14,0 cm
Package 1 Width	10,0 cm
Package 1 Length	17,0 cm
Package 1 Weight	606,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Height	11,0 cm
Package 2 Width	21,0 cm
Package 2 Length	27,0 cm
Package 2 Weight	1,212 kg
Unit Type of Package 3	S03
Number of Units in Package 3	4
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	2,451 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
SCIP broj	89350e0d-a4ac-4516-bf86-fdaed8a227fc
Uredba REACH	REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	18

Ugovorna garancija

Garancija	18 meseci
-----------	-----------