



Tehničke karakteristike proizvoda Karakteristike

83559

Mureva industrijski utikač - 16 A - 3P + N + E - 380...415 V AC - IP67

Osnovne informacije

Grupa proizvoda	PratiKa
Tip proizvoda ili komponente	Utičnica
Kratko ime uređaja	PratiKa utičnica
Kategorija priključnice i utikača	Niskonaponska
Broj polova	3P + N + E
Tip mreže	AC
Standard utičnice	Industrijski

Dopunske informacije

Način montiranja	Nadzidno
Kategorija priključnice i utikača	Pod uglom
[in] nazivna struja	16 A
[ue] nazivni napon	380...415 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	6 h
Materijal utikača, utičnice	Samogasivi konstruisan polimer
Materijal kontakta	Pinovi: poniklovan mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Poprečni presek kabla	1...4 mm ²
Kablovski uvod	Kablovska uvodnica
Tip navoja	Pg 21
Masa proizvoda	0,458 kg
Dimenzija baze	106 x 130 mm
Visina	134 mm
Širina	106 mm
Dubina	169 mm
Boja	Siva (RAL 7035)
Boja poklopca	Crvena

Okruženje

Standardi	EN 60309-1 EN 60309-2
Ip stepen zaštite	IP67 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-1
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Nadmorska visina za rad	2000 m
Temperatura okoline za rad	35 °C 86400 s) -25...40 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14,5 cm
Package 1 Width	18,0 cm
Package 1 Length	11,0 cm
Package 1 Weight	396,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Height	12,0 cm
Package 2 Width	27,0 cm
Package 2 Length	21,0 cm
Package 2 Weight	926,0 g
Unit Type of Package 3	S03
Number of Units in Package 3	6
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	3,265 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
SCIP broj	E57d0e16-20fd-447f-8324-ed3dc27095fd
Uredba REACH	REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No

Ugovorna garancija

Garancija	18 meseci
-----------	-----------