



Tehničke karakteristike proizvoda Karakteristike

83902 Mureva Wander utikač - ravni - 16 A - 3P + E - 380...415 V AC - IP44

Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Wander utičnica sa faznim invertorom
Kratko ime uređaja	Mureva plug
Kategorija priključnice i utikača	Niskonaponska
Broj polova	3P + E
Tip mreže	AC
Standard utičnice	Industrijski

Dopunske informacije

Kategorija priključnice i utikača	Ravna
[in] nazivna struja	16 A
[ue] nazivni napon	380...415 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	6 h
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Pinovi: poniklovan mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Poprečni presek kabla	1...4 mm ²
Spoljašnji prečnik kabla	8...15 mm
Kablovski uvod	Kablovska uvodnica
Tip navoja	Pg 16
Visina	139 mm
Širina	65 mm
Dubina	65 mm
Boja	Siva (RAL 7035)
Boja poklopca	Crvena

Okruženje

Standardi	IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP44 conforming to IEC 60529
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Nadmorska visina za rad	2000 m
Temperatura okoline za rad	35 °C 86400 s) -25...40 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,7 cm
Package 1 Width	6,7 cm
Package 1 Length	14,5 cm
Package 1 Weight	130,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,5 cm
Package 2 Width	21,0 cm
Package 2 Length	27,5 cm
Package 2 Weight	1,41 kg
Unit Type of Package 3	S03
Number of Units in Package 3	40
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	6,127 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
SCIP broj	661ec80b-b956-4b0a-92bb-53046f4cfb4c
Uredba REACH	REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	4

Ugovorna garancija

Garancija	18 months
-----------	-----------