



Tehničke karakteristike proizvoda

Karakteristike

83922

Mureva modularno kućište - 2 utičnice sa spojnim kutijama - 220x360

Osnovne informacije

Grupa proizvoda	Mureva
Ime proizvoda	Mureva Enclosure
Tip proizvoda ili komponente	Orman
Tip ormara	Modularna baza

Dopunske informacije

Način montiranja	Montaža na površini
Broj otvora interfejsa	2
Kablovski uvod	Definisani otvor Vodilica
Materijal	Samogasivi polimer: kućište
Masa proizvoda	1,167 kg
Dimenzija baze	103 x 225 mm
Visina	350 mm
Širina	210 mm
Dubina	70 mm
Boja	Siva (RAL 7035)

Okruženje

Standardi	IEC 60529 EN 62262 EN 60439 IEC 60695-2-1
Ip stepen zaštite	IP65 conforming to IEC 60529
Ik stepen zaštite	IK09 conforming to EN 62262
Otpornost na vatru	650 °C u skladu sa IEC 60695-2-1

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11,500 cm
Package 1 Width	36,000 cm
Package 1 Length	22,200 cm
Package 1 Weight	1,032 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	35,500 cm
Package 2 Width	24,000 cm
Package 2 Length	39,000 cm

Package 2 Weight	3,796 kg
Unit Type of Package 3	P12
Number of Units in Package 3	90
Package 3 Height	80,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	125,880 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
Uredba REACh	REACh Deklaracija
Bez SVHC-a REACh	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	9

Ugovorna garancija

Garancija	18 months
-----------	-----------