



# Tehničke karakteristike proizvoda

## Karakteristike

# 83923

## Mureva modularno kućište - 3 utičnice sa otcepnom kutijom - 340x360

### Osnovne informacije

Grupa proizvoda	Mureva
Ime proizvoda	Mureva Enclosure
Tip proizvoda ili komponente	Orman
Tip ormara	Modularna baza

### Dopunske informacije

Način montiranja	Montaža na površini
Broj otvora interfejsa	3
Kablovski uvod	Definisani otvor Vodilica
Materijal	Samogasivi polimer: kućište
Masa proizvoda	1,7 kg
Dimenzija baze	103 x 225 mm
Visina	350 mm
Širina	315 mm
Dubina	70 mm
Boja	Siva (RAL 7035)

### Okruženje

Standardi	EN 62262 IEC 60529 IEC 60695-2-1 EN 60439
Ip stepen zaštite	IP65 conforming to IEC 60529
Ik stepen zaštite	IK09 conforming to EN 62262
Otpornost na vatru	650 °C u skladu sa IEC 60695-2-1

### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11,400 cm
Package 1 Width	33,800 cm
Package 1 Length	36,100 cm
Package 1 Weight	1,460 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	2
Package 2 Height	39,000 cm
Package 2 Width	23,000 cm
Package 2 Length	35,500 cm

Package 2 Weight	5,760 kg
Unit Type of Package 3	P12
Number of Units in Package 3	40
Package 3 Height	120,000 cm
Package 3 Width	80,000 cm
Package 3 Length	77,000 cm
Package 3 Weight	70,400 kg

### Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
Uredba REACh	<a href="#">REACh Deklaracija</a>
Bez SVHC-a REACh	Da
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti okoline	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	13

### Ugovorna garancija

Garancija	18 months
-----------	-----------