



Tehničke karakteristike proizvoda

Karakteristike

A9L40182

patrona C40-1000 PV za odvodnik prenapona iPRD-DC

Osnovne informacije

Tip proizvoda ili komponente	Rezervna patrona
Kratko ime uređaja	C40-1000 PV
Tip odvodnika prenapona	Električna distributivna mreža

Dopunske informacije

Tip klase odvodnika prenapona	Tip 2
Tehnologija odvodnika prenapona	MOV
Namena proizvoda	Surge protection device iPRD PV-DC 2P
Nazivna struja pražnjenja	15 kA
Maksimalna struja pražnjenja	40 kA
[uc] maksimalni stalni radni napon	1000 V DC
Maksimalni [up] napon naponske zaštite	<2 kV tip 2
[uoc] napon otvorenog kola	833 V
Lokalna signalizacija	Zastavica (bela/crvena)
Način montiranja	Utično
Nosači za montažu	U SPD modul
9 mm redovi	2
Visina	57 mm
Širina	18 mm
Dubina	56 mm
Boja	Bela (RAL 9003)
Materijal	PBT (polibutilen-tereftalat)
Vreme odziva	< 25 ns

Okruženje

Standardi	EN 61643-11 IEC 61643-11: 2011
Oznake kvaliteta	CE
Ip stepen zaštite	IP20 prednja strana:
Relativna vlažnost	5...90 %
Nadmorska visina za rad	EcoStruxure EV Charging Expert
Temperatura okoline za rad uređaja	-25...60 °C
Temperatura okoline za skladištenje	-40...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,400 cm
Package 1 Width	7,300 cm
Package 1 Length	9,300 cm
Package 1 Weight	81,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8,000 cm
Package 2 Width	10,000 cm
Package 2 Length	28,000 cm
Package 2 Weight	1,039 kg
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	9,893 kg

Održivost ponude

Propis REACH	REACH Deklaracija
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Izjava o zaštiti životne sredine	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka

Ugovorna garancija

Garancija	18 months
-----------	-----------