



# Tehničke karakteristike proizvoda

## Karakteristike

# A9N26899

Acti 9 - pomoćni kontakt nizak nivo OF+SD - za  
C60, C120, C60H-DC, DPN, ID



### Osnovne informacije

Range of product	Acti 9
Tip proizvoda ili komponente	OC i kontakt greške
Kratko ime uređaja	OF+SD 24
Primena uređaja	For Smartlink interface
Signalni kontakt	1 NO + 1 NC
[in] nazivna struja	DC-12 2...100 mA at 24 V, DC +/- 20%
9 mm redovi	1

### Dopunske informacije

[ui] nazivni napon izolacije	500 V u skladu sa IEC 60664-1
[uimp] nazivni podnosivi impulsni napon	6 kV u skladu sa IEC 60664-1
Lokalna signalizacija	Mehanički indikator
Način montiranja	Fiksno
Nosači za montažu	DIN šina
Razvodni blok češljaste sabirnice	Donji: DA
Visina	85,5 mm
Širina	9 mm
Dubina	73,5 mm
Masa proizvoda	28 g
Boja	Bela
Električna trajnost	20000 ciklusa u skladu sa IEC 60947-5-4
Povezivanje - priključci	Priključak na oprugu Ti24 (gornji) 1 kabl(ovi) 0,5...1,5 mm <sup>2</sup> - kruti Priključak na oprugu Ti24 (gornji) 1 kabl(ovi) 0,5...1,5 mm <sup>2</sup> - fleksibilni
Dužina ogoljenog dela žice	10 mm

### Okruženje

Standardi	IEC 60947-5-4 IEC 60947-5-1
Oznake kvaliteta	CE
Stepen zaprljanosti	2 u skladu sa IEC 60664-1
Kategorija prenapona	III
Tropikalizacija	2 u skladu sa IEC 60947-5-1
Relativna vlažnost	93 % pri 40 °C
Temperatura okoline za rad uređaja	-25...70 °C
Temperatura okoline za skladištenje	-40...85 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	2 cm
Package 1 Length	9,5 cm
Package 1 Weight	36 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8,7 cm
Package 2 Width	10 cm
Package 2 Length	26,5 cm
Package 2 Weight	487 g
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4,871 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
REACH free of SVHC	Yes
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti životne sredine	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	<a href="#">Informacije O Kraju Radnog Veka</a>
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

## Ugovorna garancija

Garancija	18 meseci
-----------	-----------