



# Tehničke karakteristike proizvoda

## Karakteristike

# A9N26960

## podnaponski okidač MN 220-240VAC DC



### Osnovne informacije

Grupa proizvoda	Acti 9
Tip proizvoda ili komponente	Podnaponski okidač
Kratko ime uređaja	MN
Napon upravljačkog kola	220...240 V AC 50/60 Hz
Tip upravljanja	Standardni
9 mm redovi	2

### Dopunske informacije

Kompatibilnost grupe proizvoda	Acti9 iDPN Acti9 C120 Acti9 C40 Acti9 C60H-DC Acti9 C60NA-DC Acti9 C60PV-DC Acti9 DPN Vigi Acti9 DT40 Acti9 DT60 Acti9 ID C40 Acti9 IDc Acti9 ITG40 Acti9 ID Acti9 DPN
Lokalna signalizacija	Indikator akcije
Način montiranja	Fiksno
Nosači za montažu	35 mm simetrična DIN šina
Razvodni blok češljaste sabirnice	Gornji: DA
Visina	82,5 mm
Širina	18 mm
Dubina	73,5 mm
Masa proizvoda	66 g
Boja	Bela
Povezivanje - priključci	Vijčani priključak - 1 kabl(ovi) 2,5 mm <sup>2</sup> - fleksibilni Vijčani priključak - 1 kabl(ovi) 2,5 mm <sup>2</sup> - kruti Vijčani priključak - 2 kabl(ovi) 1,5 mm <sup>2</sup> - fleksibilni Vijčani priključak - 2 kabl(ovi) 1,5 mm <sup>2</sup> - kruti
Dužina ogoljenog dela žice	9 mm
Moment pritezanja	1 N.m
Kompatibilnost	MN

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezanost ili zavisna društva neće snositi odgovornost za zloupotrebu ovdenavedenih informacija.

## Okruženje

Standardi	EN/IEC 60947-1
Sertifikacija proizvoda	KEMA[RETURN]ASTA[RETURN]LCIE[RETURN]ASEFA
Tropikalizacija	2 u skladu sa EN/IEC 60947-5-1
Relativna vlažnost	95 % pri 55 °C
Temperatura okoline za rad uređaja	-25...50 °C
Temperatura okoline za skladištenje	-40...85 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,000 cm
Package 1 Width	7,500 cm
Package 1 Length	9,500 cm
Package 1 Weight	75,600 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	8,500 cm
Package 2 Width	10,000 cm
Package 2 Length	26,500 cm
Package 2 Weight	663,200 g
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	6,368 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	<a href="#">REACh Deklaracija</a>
EU RoHS direktiva	У складу са изузецима
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti životne sredine	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	<a href="#">Informacije O Kraju Radnog Veka</a>
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

## Ugovorna garancija

Garancija	18 months
-----------	-----------