

Tehničke karakteristike proizvoda Karakteristike

BK500EI Back-UPS 500VA 230V USB/serijski



Pregled

Vreme isporuke Usually in Stock

Osnovne informacije

Main Input Voltage	230 V
Main Output Voltage	230 V
Nazivna snaga u w	300 W
Nazivna snaga u va	500 VA
Tip proizvoda ili komponente	Uređaji za besprekidno napajanje (UPS)
Input Connection Type	IEC 60320 C14
Output connection type	3 IEC 60320 C13 1 IEC 60320 C13 preskok 2 IEC Jumpers preskok
Broj kablova	2
Tip baterije	Olovna baterija
Obezbeđena oprema	CD sa softverom CD sa dokumentacijom 1 x detachable IEC power cord 1 x detachable 1.2 m IEC power cord Telephone cable USB kabl Kartica sa garancijom

Baterija i runtime

Broj slotova napunjenih baterijama	0
Broj slotova bez baterije	0
Vreme punjenja baterije	8 sati
Broj zamena baterija	1
Napon baterije	12 V
Kapacitet baterije	7,0 Ah
Snaga punjača baterija	10 W nazivno
Snaga baterije u VAH	83 VAh kapacitet 84 VAh runtime
Životni vek baterije	4...6 godina
Produženo vreme rada	0

Opšte

Broj slobodnih slotova za modul napajanja	0
Broj popunjenih slotova za modul napajanja	0
Redundantan	No

Fizički

Boja	Bež
Visina	16,5 cm
Širina	9,1 cm
Dubina	28,4 cm
Masa proizvoda	6,32 kg
Lokacija za montiranje	Prednji deo
Odabrana ugradnja	No preference
Način montiranja	Ne može se ugraditi u rek
Montirati na dva stuba	0
USB kompatibilno	No

Ulaz

Frekvencija mreže	47...63 Hz 50/60 Hz +/- 3 Hz automatsko prepoznavanje
Ograničenje napona ulaza	160...300 V podesivi 180...266 V
Maksimalna ulazna struja	7 A
Preklopna moć	7 A

Izlaz

Maksimalna podesiva snaga u W	300 W
Izlazna frekvencija	47...63 Hz sinhronizacija na napajanje 50/60 Hz +/- 1 Hz unsynchronised
Tip UPS uređaja	Standby
Vrsta talasa	Stepped approximation to a sinewave
Maksimalna podesiva snaga u VA	500 VA
Vreme transfera	6 ms tipično : 10 ms maksimalno

Usklađenost

Sertifikacija proizvoda	C-Tick[RETURN]CE[RETURN]GOST[RETURN]VDE
Standardi	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Okolina

Temperatura okoline za rad uređaja	0...40 °C
Relativna vlažnost	0...95 %
Nadmorska visina za rad	0...10000 ft
Temperatura okoline za skladištenje	-15...45 °C
Relativna vlažnost za skladištenje	0...95 %
Nadmorska visina skladištenja	0,000000000...15240,000000000 m
Nivo zvuka	40 dBA
Toplotna disipacija	24 Btu/h

Komunikacija i upravljanje

Slobodni slotovi	0
Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Prenaponska zaštita i filtriranje

Stopa energije prenapona	310 J
Potiskivanje buke	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17,8 cm
Package 1 Width	24,1 cm
Package 1 Length	36,8 cm
Package 1 Weight	7,05 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	30
Package 2 Height	133 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	490 kg
SCC14	10731304016356

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka

Ugovorna garancija

Garancija	2 years repair or replace
-----------	---------------------------