

Tehničke karakteristike proizvoda Karakteristike

BVS500I-GR Schneider Electric EASY UPS BVS 500VA, Schuko utičnica



Pregled

Vreme isporuke	Usually in Stock
----------------	------------------

Osnovne informacije

Tip proizvoda ili komponente	Uređaji za besprekidno napajanje (UPS)
Tip baterije	Olovna baterija
Topologija	Line interactive
Količina po setu	Set od 1
Reset	Automatski reset
Grupa proizvoda	Easy UPS 1Ph BVS Series

Dopunske informacije

Tip instalacije	U zatvorenom
Surge Energy	156 J
Tip signala	Stepenasta aproksimacija sinusnog oblika
Tip zaštitnog uređaja	Surge protection device (SPD) Minijaturni prekidač (MCB) Fuse
Naponski ulaz	230 V AC
Napon izlaza	230 V
Ip stepen zaštite	IP20
Vreme transfera	6 ms tipično : 10 ms maksimalno
Mrežna frekvencija	45...65 Hz
Opseg snage	500 VA 300 W
Električna veza	Ulaz: 1 inlet šuko CEE 7/P Izlaz: 4 utičnica šuko CEE 7
Lokalna signalizacija	Alarm, distinctive za nizak nivo baterije Alarm, stalni ili isprekidani ton za preopterećenje LED za status baterije
Broj baterija	1
Vreme punjenja	8 sati
Napon baterije	12 V
Kapacitet baterije	4,5 Ah
Životni vek baterije	5 godina
Masa proizvoda	3,9 kg

Visina	92,5 mm
Širina	160,5 mm
Dubina	305 mm

Okruženje

Relativna vlažnost	0...90 %, bez kondenzacije
Nadmorska visina za rad	0...6561 ft
Temperatura okoline za rad uređaja	0...40 °C
Standardi	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Sertifikacija proizvoda	CE






Fizički

Nosači za montažu	Zid Pod
-------------------	------------

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14,500 cm
Package 1 Width	23,500 cm
Package 1 Length	37,000 cm
Package 1 Weight	3,889 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	25,000 cm
Package 2 Width	39,000 cm
Package 2 Length	58,000 cm
Package 2 Weight	17,784 kg
Unit Type of Package 3	P12
Number of Units in Package 3	48
Package 3 Height	105,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	230,408 kg
SCC14	10731304338441

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	2 years
-----------	---------