



Tehničke karakteristike proizvoda

Karakteristike

EPH0300369

Asfora - serijski prekidač, vijčani priključak, bez rama, bronza

Osnovne informacije

| | |
|------------------------------|--|
| Serija | Asfora |
| Tip proizvoda ili komponente | Prekidač |
| Prezentacija uređaja | Mehanizam sa montažnim ramom |
| Broj prekidača | 2 |
| Funkcija prekidača | Jednopolni izborni |
| Tip opterećenja | Opterećenje za štedljive svjetiljke sa balastom: 100 W |
| Nijansa boje | Bronzana |
| Tip pakovanja | Pakovanje u kesicama |

Dopunske informacije

| | |
|----------------------------|--|
| Montaža uređaja | Ugradno |
| Opseg snage | 2300 W |
| Nazivna struja | 10 AX pri 250 V AC |
| Broj kablova | 2 kabl(ovi) 2,5 mm ² |
| Krutost kabla | Fleksibilni Krući Jednožični višežični |
| Dužina ogoljenog dela žice | 13,0 mm |
| Materijal | ABS (akrilonitril-butadien-stiren) |
| Završna obrada | Ofarban |
| Provodni materijal | Bakar |
| Način fiksiranja | Zavrtnji ili kukice 51...70 mm |
| Povezivanje - priključci | Vijčani priključci |
| Širina | 71 mm |
| Visina | 71 mm |
| Dubina | 43,0 mm |
| Projektovana dubina | 15 mm |
| Masa proizvoda | 0,0652 kg |

Okruženje

| | |
|------------------------------------|-------------|
| Standardi | IEC 60669-1 |
| Sertifikacija proizvoda | VDE |
| Oznake kvaliteta | CE |
| Ip stepen zaštite | IP20 |
| Temperatura okoline za rad uređaja | -5...40 °C |

Pakovanje

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4,000 cm |
| Package 1 Width | 7,000 cm |
| Package 1 Length | 7,000 cm |

| | |
|------------------------------|-----------|
| Package 1 Weight | 66,300 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 9,500 cm |
| Package 2 Width | 18,500 cm |
| Package 2 Length | 27,500 cm |
| Package 2 Weight | 740,000 g |
| Unit Type of Package 3 | S04 |
| Number of Units in Package 3 | 120 |
| Package 3 Height | 30,000 cm |
| Package 3 Width | 40,000 cm |
| Package 3 Length | 60,000 cm |
| Package 3 Weight | 9,524 kg |

Održivost ponude

| | |
|------------------------------------|---|
| Pakovanje sa recikliranim kartonom | Da |
| SCIP broj | C6de3800-7220-4403-a6a2-26e1f05e3f4b |
| Uredba REACh | REACh Deklaracija |
| EU RoHS direktiva | Usaglašeno sa izuzecima |
| Bez žive | Da |
| Informacije o izuzeću od RoHS | Da |
| Kina RoHS regulacija | RoHS Deklaracija Za Kinu |
| Izjava o zaštiti okoline | Profil Ekološke Prihvatljivosti Proizvoda |
| Profil cirkularnosti | Nema potrebe za namenskim operacijama recikliranja |
| WEEE | Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće |